



INTEGRATED T5 | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 21695 - 16 White

[View more details](#)

TECHNICAL INFORMATION

| | |
|------------------------|---------------------|
| Watts: | 16 |
| Lumens: | 1600 |
| Shape: | T5 |
| Input Power: | AC:220-240V,50/60Hz |
| Long Life: | 25,000 Hours |
| Unit Color: | White |
| Body Type: | Plastic |
| LED Chip Type: | SMD-Samsung Chip |
| CRI: | >80 |
| Operation Temperature: | -20°C to +45°C |
| Dimmable: | No |
| Beam Angle: | 160° |
| Color Temperature: | 3000K |
| Dimension: | 1151x27x30mm |
| lumens per watt: | 100 |
| Linkable: | Upto 100W Max |



LINKABLE

T5 BATTEN FITTINGS – UP TO 100 Watts Together

Multiple units can be connected with each other, making it an efficient alternative lighting fixture for both small and big indoor areas



IP20
RATING



5 YEAR
WARRANTY



CRI>80



100
Lumen/W



SAVE UP TO
85%
ENERGY



A
F

FEATURES

- Introducing T5 Integrated Fittings designed with ON/OFF Switch.
- Linkable feature allowing you to link up to 100 watts together in series
- Fitted with high efficiency Samsung LED Chips - Save up to 85% energy
- Switch cycles: >15000
- Suitable for residential and commercial applications.



PACKAGING

| | |
|---------------------|--------------|
| Gross Weight (Kgs): | 0.25 |
| Unit CBM: | 0.0017 |
| Dimension: | 1151x27x30mm |

MASTER BOX PACKAGING

| | |
|------------------|------|
| Box Qty: | 25 |
| Length (Box) mm: | 1260 |
| Width (Box) mm: | 32 |
| Height (Box) mm: | 28 |

LISTING DETAILS

| | |
|-----------------|---------------|
| Commodity Code: | 9405114090 |
| Ean Code: | 3800157680059 |