



TECHNICAL INFORMATION

Watts:	10
Lumens:	1444
Input Power:	AC:220-240V,50/60Hz
Long Life:	20,000 Hours
Unit Color:	White
Body Type:	Aluminium
LED Chip Type:	SMD
CRI:	>80
Dimmable:	No
Beam Angle:	350°
Color Temperature:	3000K
Dimension:	230x54x96mm



FEATURES

- Well-designed 360° rotatable wall light
- Fitted with high quality LEDs for better reliability
- Efficient LED driver and intruded heat sink for longer lifespan
- Suitable for decor, restaurants, residential, facades etc.

DOUBLE HEAD ROTATABLE | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 218292 - 10 White

[View more details](#)



PACKAGING

Gross Weight (Kgs):	1.15
Unit CBM:	0.00176
Dimension:	230x54x96mm

MASTER BOX PACKAGING

Box Qty:	20
Length (Box) mm:	240
Width (Box) mm:	100
Height (Box) mm:	60

LISTING DETAILS

Commodity Code:	9405423990
Ean Code:	3800157681407