



## TECHNICAL INFORMATION

Watts:	6
Lumens:	445
Input Power:	AC:220-240V, 50Hz
Long Life:	20,000 Hours
Unit Color:	White
Body Type:	Plastic
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +45°C
Beam Angle:	110°
Color Temperature:	3000K
Equivalence Watts:	60
Dimension:	50x55mm

## GU10 LENS 110° DIMMABLE | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

*One brand, endless solutions..*

SKU: 21198 - 6 White

[View more details](#)

## LED SPOTLIGHT



Equipped with LEDs provided by Samsung for maximum efficiency.



## FEATURES

- Stable SMD-Samsung Chip technology for better reliability
- Lasts hours, longer life span than Standard halogen spotlights
- Replaces watts old halogen lamp
- Easy to install, designed with GU10 base
- Built with dimming feature
- Applications - Hotels, Bars, Commercial and Residential Lighting and Exhibition Stands etc

## PACKAGING

Gross Weight (Kgs):	0.04
Unit CBM:	0.000248
Dimension:	50x55mm

## MASTER BOX PACKAGING

Box Qty:	200
Length (Box) mm:	50
Width (Box) mm:	50
Height (Box) mm:	80

## LISTING DETAILS

Commodity Code:	8539520000
Ean Code:	3800157683371