



TECHNICAL INFORMATION

Watts:	5.8
Lumens:	425
Shape:	PAR20
Input Power:	AC:220-240V,50Hz
Long Life:	20,000 Hours
Unit Color:	White
Body Type:	Thermoplastic
PF:	>0.5
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +45°C
Beam Angle:	40°
Color Temperature:	6500K
Equivalence Watts:	55
Dimension:	64x84mm

PAR BULBS PRO | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 21149 - 5.8 White

[View more details](#)



FEATURES

- PAR20 shaped bulb for ambient lighting and aesthetics
- Fitted with high efficiency Samsung LED Chips that offer up to 85% in energy savings
- Replaces 55 watts old halogen lamp
- Lasts hours, longer life span than Standard halogen lamps
- Designed for E27 standard holder
- Suitable for residential lighting, commercial lighting, decorative, living rooms, lounges etc.

PACKAGING

Gross Weight (Kgs):	0.06
Unit CBM:	0.000446
Dimension:	64x84mm

MASTER BOX PACKAGING

Box Qty:	10
Length (Box) mm:	65
Width (Box) mm:	65
Height (Box) mm:	90

LISTING DETAILS

Commodity Code:	85395200
Ean Code:	3800157677509