



TECHNICAL INFORMATION

Watts:	4
Lumens:	400
Shape:	Candle with Twist
Input Power:	AC:220-240V, 50Hz
Long Life:	20,000 Hours
Unit Color:	Transparent
Body Type:	Glass
LED Chip Type:	Filament
CRI:	>80
Operation Temperature:	-20°C to +45°C
Dimmable:	Yes
Beam Angle:	300°
Color Temperature:	3000K
Equivalence Watts:	35
Dimension:	35x98mm



FEATURES

- Modern Clear filament Filament technology for better reliability and durability
- Replaces 35 watts old halogen lamp
- Lasts hours, longer life span than Standard halogen lamps.
- Designed for E14 standard holder
- High color rendering index CRI >80
- Suitable for residential lighting, commercial lighting, decorative, living rooms, lounges etc.

CLEAR CANDLE E14 DIMMABLE | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 214367 - 4 Transparent

[View more details](#)

CLEAR FILAMENT CANDLE BULB



No Flickering | No Mercury | No UV Radiation

PACKAGING

Gross Weight (Kgs): 0.02
Unit CBM: 0.000158
Dimension: 35x98mm

MASTER BOX PACKAGING

Box Qty: 100
Length (Box) mm: 35
Width (Box) mm: 35
Height (Box) mm: 100

LISTING DETAILS

Commodity Code: 8539520000
Ean Code: 3800157683784