



Search Klein Tools

Products

Where to Buy

Media

Support

About Klein Tools

Home » Catalog » Test & Measurement » Electrical Testers



Dual Range NCVT and Tester Electrical Test Kit NCVT5KIT

★★★★★ 4.8 (4) Write a review

- NCVT-5A provides non-contact voltage testing on cables, cords, circuit breakers, switches, and outlets, as well as AC voltage in security, environmental control and irrigation systems.
- Dual-range testing: select 120V for low voltage systems such as doorbells or irrigation systems, or select 240V for detecting systems such as electric heaters.
- NCVT-5A delivers simultaneous visual and audible indicators when AC voltage is detected.
- Audible voltage indicator beeps to indicate the higher the voltage that is sensed, the closer the source it is.
- Bright integrated laser pointer for hands-free testing at distance on the jobsite.
- RT210 detects the most common types of GFCI receptacles and outlets.
- Works on GFCI outlets and confirms if they are a fault protective device.
- Conditions the RT210 indicates: open hot, open neutral, hot/ground, hot/neutral, and correct.

BUY ONLINE



PRODUCT MEDIA

SPECIFICATIONS

WARNINGS

ACCESSORIES

RELATED ITEMS

REVIEWS

VIDEO



DOWNLOADS

- [Brochure](#)
- [NCVT Selection Guide](#)
- [Instructions](#)
- [Instructions](#)
- [Safety Data Sheet](#)

IMAGES

[Products](#)[Where to Buy](#)[Media](#)



[Support](#)[About Klein Tools](#)



[INTERACTIVE CATALOG](#)
[Product Page](#)
[Product Section](#)

The NCVT5KIT includes a dual-range non-contact voltage tester with laser pointer and a GFCI receptacle tester. The NCVT-5A auto voltage (12 - 1000V) allowing broad application. The RT210 will troubleshoot the most common wiring problems in standard and

Specifications

Type:	Non-Contact AC Voltage Tester, GFCI Receptacle Tester	Included:	NCVT-5A Dual Range Tester; RT210 GFCI R Instructions; and All f
Application:	Dual-Range Non-contact Detection of the Presence of AC Voltage from 12-1000 VAC or from 70-1000V AC	Batteries:	2 x AAA
Special Features:	Integrated High Strength Red Laser Pointer, Dual Range Tester (70-1000V; 12V-1000V) AC Voltage Detection, Simultaneous Visual and Audible Voltage Indicators in the Presence of AC Voltage; US Patent No. D750985	Battery Life:	Laser On: 31 hr; NCV Alerts: 25 hr
Material:	Plastic and Electronic Assemblies	Overall Length:	6" (15.2 cm)
Drop Protection:	9.8' (3 m)	Overall Height:	0.96" (2.4 cm)
Voltage:	12 to 1000 VAC	Overall Width:	1.16" (2.9 cm)
Frequency:	50 to 500 Hz	Weight:	1.5 oz (43 g)
Pollution Degree:	2	UPC:	092644692369
Standard:	CAT IV 1000V; Laser: Class 3a, 630-670nm, Max Power <5mW		

Additional Information

[Products](#)[Where to Buy](#)[Media](#)[Support](#)[About K](#)

WARNINGS

- Read, understand, and follow all instructions, cautions and warnings attached to and/or packed with all test and measurement
- Never assume neutral or ground wires are de-energized. Neutrals in multi-wire branch circuits may be energized when disconnected before handling.
- LASER RADIATION, Class 3a laser. DO NOT direct laser beam into eyes, DO NOT stare into the beam, or DO NOT view directly can cause severe and permanent eye damage.
- Use of this tester in any way other than that specified by the manufacturer can impair safe operation, resulting in severe injury

ACCESSORIES



RT210
GFCI Outlet Tester
★★★★★ 5.0 (4)

RELATED ITEMS



ET250
AC/DC
Voltage/Continuity
Tester
★★★★★ 4.7 (3)



ET60
Electronic AC/DC
Voltage Tester, 12 to
600V
★★★★★ 5.0 (1)



ET45VP
AC/DC Voltage and
GFCI Receptacle Outlet
Test Kit
★★★★★ 5.0 (5)



NCVT2P
Dual Range Non-
Contact Voltage Tester
12 - 1000V AC
★★★★★ 5.0 (5)

★★★★★ 4.8 | 4 Reviews

4 of 4 (100%) reviewers recommend this product

