

Between Series Adaptor 33_QMA-N-50-1/133_N

Description

Adaptor plug/jack
QMA plug (male) / N jack (female)

QuickLock Interface

Interface standards
Series QMA - QMA QLF compliant
Series N - IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz
Frequency range	DC to 6 GHz
Return loss	≥ 34 dB

Mechanical Data

Number of matings	100
Weight	0.0249 kg

Environmental Data

Operating temperature	-40 °C to 85 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - QMA plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00013987
-----------------	--------------

Ordering Information

Single package	33_QMA-N-50-1/133_NE
----------------	----------------------