



3 pole female XLR receptacle with solder lugs





Article Variations

Article Name	Details	Packaging
RC3FDL	Nickel plated housing, tin plated contacts	
RC3FDL-B	Black plated housing, gold plated contacts	



Technical Information

Product	
Title	RC3FDL
Connection Type	XLR
Gender	female

Electrical		
Insulation Resistance	>1 GΩ	
Contact Resistance	≤5 mΩ	
Rated Current	≤10 A	

Mechanical	
Lifetime	>1000 Mating Cycles
Insertion Force	≤20N
Withdrawal Force	≤20N

Material	
Ground Contact	Bronze
Jack	Bronze
Housing	Zinc
Latch	Steel
Spring	Steel
Plastic Body	PA6+30%GF
Ground Contact	Tin and Cer
Jack	Tin and Cer
Housing	Nickel Plating
Latch	Nickel Plating