

## NYS229

1/4" open jack, mono 2 pole, with washer and nut, with 0.205" faston tabs



### Article Variations

Article Name	Details	Packaging
NYS229	for up to 3.5 mm panel thickness	
NYS229L	for up to 6.5 mm panel thickness	

## Technical Information

### Product

<b>Title</b>	NYS229
<b>Connection Type</b>	Jack

### Electrical

<b>Contact resistance</b>	$\leq 10\text{m}\Omega$
<b>Insulation resistance</b>	$\geq 2000\text{M}\Omega$
<b>Dielectric strength</b>	50Hz 500VAC

### Mechanical

<b>Insertion and Withdrawal force</b>	4.5-40N
<b>Lifetime</b>	>5000 mating cycles

### Material

<b>Contact</b>	QSn6.5-0.160.5 T
<b>Contact</b>	H62 60.5 Y2
<b>Base</b>	Brass
<b>Gasket</b>	Steel
<b>Nut</b>	Brass
<b>Contact</b>	Tin and Ce
<b>Contact</b>	Tin and Ce