



Mono 2 pole 3.5 mm plug, crimp strain relief















Article Variations

Article Name	Details	Packaging
NYS226	metal handle	
NYS226B	black plated metal handle	
NYS226BG	black plated metal handle, gold plated contacts	
NYS226G	metal handle, gold plated contacts	
NYS226L	metal handle, large cable outlet	
NYS226LBG	black plated metal handle,gold plated contacts,large cable outlet	



Technical Information

Product		
Title	NYS226	
Connection Type	Plug	

Electrical			
Contact Resistance	≤10 mΩ		
Insulation Resistance	>200 MΩ(Initial)		
Dielectric Strength	500V dc 50HZ		

Mechanical		
Cable O.D.	max 4.5mm for standard outlet max 6.4mm for large outlet (* L)	
Insertion and Withdrawal Force	≤60 N	
Lifetime	>1,000 Mating Cycles	

Material		
Plug finger	Brass	
Sleeve	Zinc	
Cable Clamp	Steel	
Housing	Zinc	
Insulation	РР	
Plug finger plating	Nickel	
Sleeve plating	Nickel	
Cable Clamp plating	Tin	
Housing plating	Nickel	