



3 pole DIN cable connector, male





## **Article Variations**

Article Name	Details	Packaging
NYS321	silver plated contacts	
NYS321G	gold plated contacts	



## **Technical Information**

Product	
Title	NYS321
Gender	male

Electrical	
Contact Resistance	≤10 mΩ
Insulation Resistance	>1000 MΩ(Initial)
Rated Voltage	50 VAC

Mechanical	
Insertion and Withdrawal Force	3-24N
Lifetime	>1000 Mating Cycles
Cable O.D.	< 6.5 mm

Material	
Pin	Brass
Boot	PVC
Housing	Zinc
Wire locker	Steel
Screw	Brass
Pin Holder	PA6
Pin	Silver Plated
Wire locker	Nickel
Screw	Nickel