

NYS322

5 pole DIN cable connector, male



Article Variations

Article Name	Details	Packaging
NYS322	silver plated contacts	
NYS322G	gold plated contacts	
NYS322AG	gold plated shell and contacts	

Product

Title	NYS322
Gender	male

Electrical

Contact Resistance	<10 mΩ
Insulation Resistance	>1000 MΩ(Initial)
Dielectric Strength	500V dc
Rated Voltage	50 VAC

Mechanical

Insertion Force	≤40N
Withdrawal Force	>5.5N
Lifetime	>1000 Mating Cycles
Cable O.D.	< 6.5 mm

Material

Pin	Brass
Pin Holder	PA6+30%GF
Screw	Steel
Cable Clamp	Steel
Housing	Zinc
Boot	PVC
Pin	Silver Plating
Screw	Nickel Plating
Cable Clamp	Nickel Plating
Housing	Nickel Plating