

NYS323

7 pole DIN cable connector, male



Article Variations

Article Name	Details	Packaging
NYS323	silver plated contacts	
NYS323G	gold plated contacts	

Technical Information

Product	
Title	NYS323
Gender	male

Electrical	
Contact Resistance	<10 mΩ
Insulation Resistance	>1000 MΩ(Initial)
Dielectric Strength	500V dc
Rated Voltage	50 VAC

Mechanical	
Insertion Force	≤56N
Withdrawal Force	>7.5N
Lifetime	>1000 Mating Cycles
Cable O.D.	< 6.5 mm

Material	
Pin	Brass
Pin Holder	PA6+30%GF
Screw	Steel
Cable Clamp	Steel
Housing	Zinc
Boot	PVC
Pin	Silver Plating
Screw	Nickel Plating
Cable Clamp	Nickel Plating
Housing	Nickel Plating