



LOC	DIST	P	F	REVISIONS				
				ZONE	LTR	DESCRIPTION	DATE	APPD
AF	50				G	REV PER 0G1A-0148-99	4JUN99	JR/JH





- 1 MATES WITH .032±.001×.187 TAB
- 2 WIRE STRIP LENGTH .281
- 3 INSULATION SIZE .090-.160 DIA
- 4 DIMENSION DOES NOT INCLUDE TRIM BURR
- 5 .015 MAX CARRIER TRIM BURR PER SIDE IS ALLOWABLE IN THE SHADED AREA



.010 MAX
CUT-OFF
TAB

WIRE AND RECEPTACLE
SIZE IDENTIFICATION
16-14
187
AMP



HOUSING: NYLON, COLOR-BLUE TRANSLUCENT RECEPTACLE: #3 HARD BRASS TIN PL .000080 MIN THK				3-520412-2	
MATERIAL & FINISH				PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLC DEC ± -. 3 PLC DEC ± .015 ANGLES ± -. MATERIAL SEE TABLE	DR 11/2/88 P FORTNEY	AMP AMP INCORPORATED Harrisburg, Pa. 17105			
	CHK 11/2/88 MS FEHER				
	APPD 11/2/88 K RANDOLH	NAME RECEPTACLE ASSY, ULTRA-FAST PLUS, LOOSE PIECE .187 SERIES, 16-14 AWG			
	APPD 11/14/88 T SHUTTER				
	PRODUCT SPEC 108-2044				
FINISH SEE TABLE	APPLICATION SPEC 114-2123	SIZE B	F5CM NO 00779	DRAWING NO 520412	
	WEIGHT -	SCALE 4:1	SHEET 1 OF 1		