

Model: IQC5000VC-W**3 YEAR Warranty** 

Part Number: Model: IQC5000VC-W

Product Group: CCTV

Product Type: Hybrid Dome Camera

**5MP 4in1 HD/Analogue Colour Night View Vandal Eyeball/Turret Dome Camera**

Style	Colour Night View Vandal Eyeball/Turret Dome Camera
Weather Resistant	Yes (IP66)
Vandal Resistant	Yes
Mounting Type	Wall or Ceiling
Sensor	1/2.8" 5MP SONY Starvis CMOS
DSP Functions	Automatic White Balance, 120dB Wide Dynamic Range, 3D Digital Noise Reduction, Starlight, Privacy Masking, Motion Detection
Video Formats Supported	AHD, HD-TVI, HD-CVI, CVBS
Resolution	5MP
Lens Type	Fixed
Lens Size	3.6mm
Viewing Angle	89°
Colour Night Vision	20m White Light
Minimum Illumination	0.05 lux@F1.2 (AGC ON), 0 Lux with IR ON

Operating Voltage	12V DC
UTC Support	Yes
Video Output	BNC Socket
Audio Output	No
Power Input	DC Socket (2.1mm)
Power Consumption	<5W
RS485 Control	No
Operating Temperature	-10 to 60°
Operating Humidity	<90%
Dimensions (WHD)	93.2 x 81.71 x 105.9mm
Weight (kg)	0.4
Warranty	3 Year Warranty

Accessories

Junction Box (Model: IQC5000VC-JB)

