

Model: IQC8000V-W**3 YEAR Warranty** 

Part Number: Model: IQC8000V-W

Product Group: CCTV

Product Type: Hybrid Dome Camera








8MP (4K) 4in1 HD/Analogue Vandal Eyeball/Turret Dome Camera

Style	Eyeball/Turret Dome Camera
Weather Resistant	Yes (IP66)
Vandal Resistant	Yes
Mounting Type	Wall or Ceiling
Sensor	1/2.7" Progressive CMOS
DSP Functions	Back Light Compensation, Automatic White Balance, DWDR, Starlight, 3D DNR, Automatic Electronic Shutter Speed, Mirror
Video Formats Supported	AHD, HD-TVI, HD-CVI, CVBS
Resolution	8MP (3840 x 2160)
Lens Type	Fixed
Lens Size	2.8mm
Viewing Angle	99°
Night Vision	40m Smart IR
Minimum Illumination	0.05 lux@F1.2 (AGC ON), 0 Lux with IR ON
Operating Voltage	12V DC

UTC Support	Yes
Video Output	BNC Socket
Audio Output	No
Power Input	DC Socket (2.1mm)
Power Consumption	IR ON: 5W/IR OFF: 1.5W
RS485 Control	No
Operating Temperature	-30 to 55°
Operating Humidity	90%
Dimensions (WHD)	Ø100 x 90.3mm
Weight (kg)	0.44
Warranty	3 Year Warranty

Accessories

Junction Box (Model: JB-VBED-W)	
Junction Box (Model: JB-001)	
Junction Box (Model: JB-003)	
Junction Box (Model: JB-005)	
Wall Bracket (Model: WB-001)	
Wall Bracket (Model: WB-005)	