

Model: IQC8000VV-G**3 YEAR Warranty** 

Part Number: Model: IQC8000VV-G

Product Group: CCTV

Product Type: Hybrid Dome Camera

**8MP (4K) 4in1 HD/Analogue Varifocal Vandal Eyeball/Turret Dome Camera**

Style	Eyeball/Turret Dome Camera
Weather Resistant	Yes (IP66)
Vandal Resistant	Yes
Mounting Type	Wall or Ceiling
Sensor	1/2.7" Progressive CMOS
DSP Functions	Back Light Compensation, Automatic White Balance, DWDR, Automatic Gain Control, Starlight, 3D DNR, Automatic Electronic Shutter Speed, Mirror
Video Formats Supported	AHD, HD-TVI, HD-CVI, CVBS
Resolution	8MP (3840 x 2160)
Lens Type	Varifocal
Lens Size	2.7-13.5mm
Viewing Angle	34-116°
Night Vision	60m Smart IR
Minimum Illumination	0.05 lux@F1.2 (AGC ON), 0 Lux with IR ON
Operating Voltage	12V DC

UTC Support	Yes
Video Output	BNC Socket
Audio Output	No
Power Input	DC Socket (2.1mm)
Power Consumption	IR ON: 5W/IR OFF: 1.5W
RS485 Control	No
Operating Temperature	-30 to 50°
Operating Humidity	90%
Dimensions (WHD)	Ø126 x 102.51mm
Weight (kg)	0.96
Warranty	3 Year Warranty

Accessories

Junction Box (Model: JB-004)	
Junction Box (Model: JB-006)	
Wall Bracket (Model: WB-006)	