

## Model: IQR8000D4H

### 3 YEAR Warranty



Part Number: Model: IQR8000D4H

Product Group: CCTV

Product Type: Hybrid DVR



## 8MP (4K) 4 Channel (+2 IP) Hybrid 5in1 H265 DVR

Video Input	4 Channel BNC
Audio Input	4 Channel RCA
Audio Output	1 Channel RCA
IP Camera Support	2 Channel
Video Output/Resolution	1x BNC (Max. 704x576), 1x VGA (Max. 1080P), 1x HDMI (Max. 4K)
Display Split	1/4/6/SEQ
Video Formats Supported	8MP/5MP/4MP/1080P/720P/960H
Compression	Audio: G.711a, Video: H.264/H.265
Recording Resolution and Frame Rates (per channel)	Analogue: 8MP-7fps, 5MP-12fps, 4MP – 15fps, 1080P - PAL-25fps/NTSC-30fps IP: PAL-25fps/NTSC-30fps Sub-stream Max: PAL-704x576:10fps/NTSC-704x480:10fps
Recording Modes	Continuous/Manual/Motion Detection
IP Recording Bandwidth (Min-Max)	12Mbps – 36Mbps
Sync Playback	4 Channel
Backup Mode	Network/USB
Ethernet	RJ45 10/100M

Network Monitoring	Internet Explorer, CMS, Android & iOS App (XIQ Mobile CMS)
Internal Hard Drive	1 SATA HDD, Up to 8TB
Alarm Input/Output	4 in/1 Out
PTZ Control	RS485
USB Interface	2 (1x Front/1x Rear)
Power Supply	DC 12V/2A
Operating Temperature	0 to 40°
Operating Humidity	<90%
Dimensions (WHD)	300 x 53 x 227mm
Warranty	3 Year Warranty