



Woodworking - Orbital Sanders - Palm Sander

D26441



D26441 Features

- 230 Watt motor sands at 14,000 orbits per minute, providing a superior finish
- Hook & loop platen allows faster paper change, better dust extraction and increase sanding efficiency
- Paper clamps provided for conventional abrasives
- Textured anti-slip top and body grip provides ultimate comfort and control during prolonged use
- Dust sealed switch for increased durability
- Sealed 100% ball-bearing construction provides longer life
- High capacity dust bag with built in vacuum adaptor provides maximum dust collection with or without vacuum
- Dual plane counter-balance low-vibration design reduces user fatigue

D26441 Specifications

Power Input	230 Watts
Power Output	120 Watts
Rotation speed	14000 rpm
Orbits Per Minute	28000 opm
Orbit Size	1.4 mm
Paper Size	140x115 mm
Pad Size	108x115 mm
Weight	1.4 kg
Length	130 mm
Height	160 mm

D26441 Standard

- Sanding sheets
- Paper punch
- Dust bag with built-in extractor connection