



Metal Working Tools - Small Angle Grinders - 115mm DEWALT SAG

D28113



D28113 Features

- Dust ejection system removes majority of debris from the air which passes over the motor, preventing abrasion and tracking
- Anti vibration side handle to improve user comfort
- New guard design allows guard fitment, adjustment or removal without the use of tools, for increased flexibility
- Fully leaded stator windings for increased motor durability
- Pop off brushes protect the armature from damage at the end of brush life resulting in greater motor durability
- Small girth allow comfortable gripping resulting in superior ergonomics
- The low profile gear case allows access in confined areas
- Abrasion protected motor for increased durability
- Anti lock flange prevents flanges from permanently locking up and locking the disc on
- One piece brush arm prevents brush hang up in extreme conditions
- Side positioned spindle lock gives greater protection to button when using in confined spaces

D28113 Specifications

Power Input	900 Watts
No Load Speed	10000 rpm
Max. Disc Diameter	115 mm
Spindle Thread	M14
Weight	2.1 kg
Length	285 mm
Height	80 mm

D28113 Standard

- Protective keyless guard
- Multi-position anti vibration side handle
- Inner and outer disc flange
- Spanner