



Cordless - Drill and Drivers - 14.4 Volt 10 mm Cordless Drill Driver

DC728KA



DC728KA Features

- Powerful 14.4 Volt drill driver for drilling and screwdriving applications
- Compact, lightweight design
- 17 position adjustable torque control for consistent screwdriving into a variety of materials with different screw sizes
- Two speed settings, variable speed and reverse switch for controllable use
- Ergonomically designed trigger and rubber grip
- 10 mm single sleeve keyless chuck with automatic spindle lock for quick and easy bit change with one hand
- Electronic motor brake for added control
- High performance fan cooled motor for maximum power and durability
- All metal gearing for efficient power transmission and longer tool life
- Modular design for easy access to key components and excellent serviceability

DC728KA Specifications

Voltage	14,4 V
Battery Capacity	NiCd 1.3 Ah
Chuck Capacity	1.5-10 mm
Power Output	290 Watts
No Load Speed	0-400 / 0-1400 rpm
Max Torque	35 Nm
Max. Drilling Capacity [Wood]	32 mm
Max. Drilling Capacity [Metal]	10 mm
Spindle Thread	
Weight	1.9 kg
Length	218 mm
Height	229 mm

DC728KA Standard

- 1 hour charger
- 2 batteries
- Heavy duty carrying case