

## Product image



## Technical details

### Description

Designation optional Two-cutter, 4 flute

### Details

Diameter (D) mm	10
Working length (L1) mm	950
Total length (L2) mm	1000
Material, short name	TC
Drill bit, use	Hammer drill bits
Shaft, shape	SDS-plus
Material that can be processed	Stone/concrete
Materials that can be processed, other	Masonry
Drill bit, shape	four flutes - S4
Cutter, type	Two-cutter
Cutting direction	right

Sales package qty: 1 Units  
Despatch package qty: 1  
Bulk package quantity:  
20 Units  
Part No.: 2 608 597 122

PU: Packaging unit; PT: Packaging type; IPU: Interim packing unit; DPU: Despatch packaging unit; GPE: Masterpack