

SPARE PARTS LIST

MODEL NO. JR3070CT

ITEM	PART NO.	DESCRIPTION	QTY	NOTE
001	163453-5	SHOE JR3070CT	1	
002	421904-7	INSULATION COVER JR3070CT	1	
003	421894-4	PROTECTOR JR3050T/3060T/3070CT	1	
004	257952-8	RETAINING RING BJR181SFE	1	
005	310160-3	DRIVING SLEEVE JR3050T/JR3060TJR3070CT	1	
006	268094-3	PIN 3 BHR240/JR140D/180D/3070CJR3060T	1	
007	331720-8	GUIDE SLEEVE BJR181SFE	1	
008	417791-0	DRIVING SLEEVE GUIDE BJR240/JRJR3060T/3070CT	1	
009	418311-3	SLEEVE BJR240/JR140D/180D JR3060T/3070CT	1	
010	345214-7	PUSH PLATE BJR240/JR140D/JR180JR3060T/3070CT	1	
011	233025-1	COMPRESSION SPRING 2 6702D/670BFL080/121FZ/JR3060T/3070CT	1	
012	231687-9	TORSION SPRING 17 JR3060T/70CTJR3060T/3070CT	1	
013	257742-9	SHOULDER SLEEVE 14 JR3060T JR3070CT	1	
014	213174-0	X RING 14 JR3030T/JR3050T/3060JR3070CT	1	
015	911225-0	*PAN HDSCREW M5X16 W/SP 10PK WASHER	4	
016	418806-6	CAP JR3050T/JR3060T/3070CT	1	
017	961012-7	*EXT E-RING JIS JE-6 10PK LF1000	1	
018	154551-6	GEAR HOUSING CO JR3060T-3070CTJR3060T/3070CT	1	
019	961012-7	*EXT E-RING JIS JE-6 10PK LF1000	1	
020	154502-9	SLIVER SUPPORT COMP JR3060T-70JR3070CT	1	
021	233038-2	COMPRESSION SPRING 5 AN942 JR3060T/JR3070CT	2	
022	423343-7	SEAL PLATE 14 JR3060T/70CT JR3060T/JR3070CT	1	
023	214170-1	PLANE BEARING 14A JR3060T/3070	1	
024	154804-3	SLIDER COMP JR3060T/JR3070CT	1	
025	345487-2	SLIDE PLATE JR3060T/3070CT	1	
026	317842-8	GEAR HOUSING JR3060T/3070CT	1	
027	154547-7	BEARING COMP JR3060T-3070CT	1	
028	345486-4	PLATE B JR3060T/3070CT	1	
029	911225-0	*PAN HDSCREW M5X16 W/SP 10PK WASHER	2	
030	265530-0	HEX SOCKET HD BOLT M5X8 JR3060JR3070CT	3	
031	951051-5	*TENSION PIN3-8 DIN 1481 10PK	1	
032	911225-0	*PAN HDSCREW M5X16 W/SP 10PK WASHER	3	
033	317844-4	BEARING BOX JR3060T/3070CT	1	
034	211101-1	BALL BEARING 6001LLB JR3060T JR3070CT	1	
035	345488-0	GEAR PLATE JR3060T/JR3070CT	1	
036	213726-7	O RING 62 JR3060T/JR3070CT	1	
037	154549-3	TORQUE LIMITER JR3060T-3070CT	1	
038	266012-5	*PT SCREW 5X35 HR160D 10PK	4	
039	265165-7	TORX SOCKET HD SCREW M6X16 BJR	1	
040	345479-1	SHOE GUIDE JR3050T/3060T/3070C	1	
041	232222-6	LEAF SPRING B JR3050T/JR3060T JR3070CT	1	
042	911225-0	*PAN HDSCREW M5X16 W/SP 10PK WASHER	2	
043	345485-6	PLATE A JR3060T/JR3070CT	1	
044	265531-8	HEX SOCKET HD BOLT M6X14 JR306JR3070CT	1	
045	154545-1	CRANK CAM COMP JR3060T-3070CT	1	
046	257265-7	RING 21 JR3070CT	1	
047	313121-2	COUNTER WEIGHT JR3070CT	1	
048	154546-9	CRANK BASE COMP JR3060T-3070CT	1	
049	345489-8	GUIDE PLATE JR3070CT	1	
050	211251-2	BALL BEARING 6003LLB 4603DW JR3060T/JR3070CT	1	
051	265148-7	TORX SOCKET HEAD SCREW M5X14 JR3070CT	4	
052	212957-5	NEEDLE BEARING 710 JR3060T/70CJR3070CT	1	
054	418991-5	STOPPER JR3060T /3070CT	1	
055	231309-1	*COMPRESSION SPRING 5 5PK	1	
056	272247-8	LEVER 20 JR3060T/3070CT	1	
057	213021-5	O RING 5 LS800DWB/M241/BLS820 JR3060T/3070CT	1	

SPARE PARTS LIST

MODEL NO. JR3070CT

ITEM	PART NO.	DESCRIPTION	QTY	NOTE
058	213021-5	O RING 5 LS800DWB/M241/BLS820 JR3060T/3070CT	1	
059	413095-8	PLATE C JR3060T/JR3070CT	1	
060	421899-4	SEAL RING JR3060T/3070CT	1	
061	268012-1	PIN 7 JR3020/JR3060T/3070CT	1	
062	162236-0	SHIFT BUTTON JR3050T/JR3060T JR3070CT	1	
063	232221-8	LEAF SPRING A JR3050T/JR3060T JR3070CT	1	
064	256158-5	PIN 3 T221DW/6835DWA/BLS820/JRJR3060T/3070CT	1	
065	233345-3	COMPRESSION SPRING 6 BJR240 JT3060T/3070CT	1	
066	256492-3	SHOULDER PIN 5 J3060T/70CT	1	
067	961052-5	*EXT DIN 471 CIRCLIP-12 10PK	1	
068	253744-3	*HARD WASHER 12 10PK	1	
069	211131-2	BALL BEARING 6001DDW 8412DWA/JHR2432/JR3060T/3070CT	1	
070	253744-3	*HARD WASHER 12 10PK	1	
071	285719-4	BEARING RETAINER A JR3060T/307	1	
072	241863-7	FAN HR3000C/JR3060T/3070CT	1	
073	513603-6	ARMATURE ASSY 240V JR3070CT INC. 72,74,75	1	240V
074	681650-6	INSULATION WASHER HR4000C HR3000C/JR3070CT	1	
075	210029-0	BALL BEARING 608ZZ MT811 JR3060T/3070CT	1	
076	266056-5	*PT SCREW 5X45 9046 5PK	2	
077	418817-1	BAFFLE PLATE JR3060T/JR3070CT	1	
078	525718-7	FIELD ASSY 240V JR3070CT	1	240V
079	154498-4	MOTOR HOUSING COMP JR3050T-70CJR3060T/3070CT	1	
080	650222-8	SWITCH TG71ARS-1 JR3060T/70T	1	
081	265995-6	*PT SCREW 4X18 10PK LF1000	5	
082	183933-5	HANDLE SET JR3070CT INC. 100	1	
083	692502-6	POWER SUPPLY CORD 1.0-2-4.0 HR2432/JR3060T/JR3070CT	1	240V
084	265995-6	*PT SCREW 4X18 10PK LF1000	2	
085	687052-4	STRAIN RELIEF 4157KB/2414B/JR3LS1230/BO6040/190/GD0800C/2#32	1	240V
086	682573-1	CORD GUARD 10 GA7010/9010/SA7 JR3060T/3070CT	1	
087	645253-0	NOISE SUPPRESSOR RP1100/HK0500DA3000R/HR2432/JR3050T	1	240V
088	645006-7	NOISE SUPPRESSOR/CONDENSOR 645JR3060T/3070CT/LF1000	1	240V
089	646049-2	CHOKE COIL HR2420/JR3060T/3070	1	240V
092	631651-4	CONTROLLER JR3070CT	1	240V
093	213261-5	O RING 17 9207SPC/9217SPC/HR24JR3070CT	1	
094	418905-4	DIAL JR3070CT	1	
095	418518-1	SLEEVE GA7010/9010/SA7000C JR3070CT	1	
096	421448-7	RUBBER BAND JR3020/3060T/PP200JR3070CT	1	240V
097	861231-4	NAME PLATE JR3070CT	1	
098	191963-2	CARBON BRUSH CB-303 5703R/9920JR3060T/3070CT	1	
099	643750-0	BRUSH HOLDER CAP JR3020/9920/5JR3060T/3070CT	2	
100	183933-5	HANDLE SET JR3070CT INC. 82	1	
A01	824734-9	PLASTIC CARRYING CASE JR3050T JR3060T/3070CT	1	
A02	B-05038	RECIPRO BLADE SA123XF METAL	1	
A03	B-05044	RECIPRO BLADE SA345XF UNIVERSA	1	
A04	B-05153	RECIPRO BLADE 203X18X1.0 WOOD	1	
E01	655030-2	*PLUG UK TYPE 2107F/JR3050T HM1810/HR2432/JR3060T/3070CT	1	110V
E02	654091-9	NON INSULATED TERMINAL LC1230 N910/RP0910/HM1810/HR2432/JR3060T/3070CT	1	110V

SERVICE DRAWING

MODEL NO. JR3070CT

