

Steel scriber

DELA.1586.00

- Plastic body.
- Tip \varnothing 4 mm.
- Body \varnothing 8 mm.
- Length 210 mm.
- $\Delta\Delta$: 20 g.



Carbide pen scriber

DELA.1589.00

- Hexagonal steel body with clip.
- Re grindable tip, length 12 mm, \varnothing 2.5 mm.
- Length 150 mm.
- $\Delta\Delta$: 35 g.



Retractable carbide scriber

233A

- Body with clip.
- Double-dressed tungsten-carbide tip.
- Length 145 mm.
- Tip \varnothing 2 mm.
- Body \varnothing 8 mm.
- $\Delta\Delta$: 16 g.



	Description
233.P5	Set of 5 spare tips

Monobloc carbide scriber

236

- Inset tungsten-carbide tip for marking hard surfaces \varnothing 2 mm.
- Octagonal body \varnothing 12 mm.
- Length 180 mm.
- $\Delta\Delta$: 30 g.



Square tips

- Hardened steel point, square blade. Isoryl handle. For starting holes, chamfering, deburring, etc.

	Handle \varnothing x L mm	Length mm	Blade \square x L mm	$\Delta\Delta$ g
AP.6x80	30 x 110	190	6 x 80	72
AP.8x125	34 x 120	245	8 x 125	132

AP.8x125



▶ Measuring and marking-out module

Measuring and marking-out module

MOD.234

- 257G. Automatic centre punch.
- 234 Scriber.
- 893.316 Tape measure 3 m.
- DELA.1051.05 Rule 300 mm long.
- DELA.1885.00 Protractor.
- DELA.1223.02 Try and mitre square 300 mm long.
- Tray PL.633.
- $\Delta\Delta$: 1.05 kg.

