

# Eaton 10250T15112H639-1

Catalog Number: 10250T15112H639-1

Eaton 10250T pushbutton, 10250T, Selector switch, 30.5 mm, Metal, Cam 1, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Two-position, Maintained, Key, 1NO-1NC, Left only, H639, Chrome bezel

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T15112H639-1
UPC	Product Length/Depth
782113500669	1 in
Product Height	Product Width
1 in	1 in
Product Diameter	Product Weight
1.38 in	.1 lb
Warranty	Compliances
1 year	CE Marked
Certifications	
CSA Certified UL Listed	



## Product specifications

### Product Category

Selector switch

### Contact configuration

1 NO-1 NC

### Throw type

60 °

### Number of positions

2

### Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

### Bezel

Chrome

### Key code

H639

### Series

10250T

### Type

30.5 mm, metallic

### Operating mode

Maintained

### Illumination

Non-illuminated

### Cam code

Cam 1

### Key removal position

Left only

### Actuator

Key

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T15112H639-1



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)