

Eaton C25DNJ350A

Catalog Number: C25DNJ350A

Eaton definite purpose contactor, Quick, 50A, 550-600 Vac, 50/60 Hz, 1NC, Open with metal mounting plate, 15-50A, two- and three-pole, 50A, Contactor, Three-pole, 65A, Box lugs(posidrive setscrew) and quick connect terminals , Non-reversing

General specifications

| | |
|----------------------------------|--|
| Product Name | Catalog Number |
| Eaton definite purpose contactor | C25DNJ350A |
| UPC | Product Length/Depth |
| 782116300723 | 3.35 in |
| Product Height | Product Width |
| 3.75 in | 2.4 in |
| Product Weight | Warranty |
| 1.3 lb | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| Compliances | Certifications |
| CE Marked RoHS Compliant | CSA Certified UL Listed file E1491 (Guide Number NLDX2) |



Product specifications

Inductive full load

50 A

Auxiliary contacts

Quick connect (vertical in-line)

Connection

Quick

Enclosure

Open with metal mounting plate

Number Of Poles

Three-pole

Coil

110-120 Vac

Frame size

15-50 A, two-pole and three-pole

Accessories

Mounting plate

Coil voltage

50/60 Hz

Series

E1

Type

Non-reversing

Model

Contactors

Terminals

Box lugs (posidrive setscrew)

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[C25DNJ3 3D Inventor](#)

[C25DNJ3 AutoCAD 2D Footprint \(mm\)](#)

[C25DNJ3 2D Drawing Xchange](#)

[C25DNJ3 AutoCAD 2D Footprint](#)

[C25DNJ3 2D PDF](#)

[C25DNJ3 3D Model Xchange](#)

Specifications and datasheets

[Eaton Specification Sheet - C25DNJ350A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)