

Eaton 10250T15112H620-1

Catalog Number: 10250T15112H620-1

Eaton 10250T, Selector switch, 30.5 mm, Chrome bezel, Heavy-Duty, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Key, Two-position, Vertical, 1NO-1NC, H620, Left only

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T15112H620-1
UPC	Product Length/Depth
782113500546	2.5 in
Product Height	Product Width
1.75 in	1.75 in
Product Weight	Warranty
.39 lb	1 year
Compliances	Certifications
CE Marked	UL Listed CSA Certified

Catalog Notes

With H Series Lock and Key Code: H620



Product specifications

Product Category

Selector switch

Throw type

60 °

Contact configuration

1 NO-1 NC

Number of positions

2

Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Mounting method

Vertical

Bezel

Chrome

Key code

H620

Series

10250T

Type

Pushbutton

Illumination

Non-illuminated

Cam code

Cam 1

Key removal position

Left only

Actuator

Key

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T15112H620-1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)