

# Eaton XTCE025C01TD

Catalog Number: XTCE025C01TD

Eaton XT IEC contactor, 25A, 24-27 Vdc, 1NC, 25A, Frame C, 45 mm, 2, 3, 5/ 7.5, 10, 15, 20 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Non-reversing, XT IEC series, Screw terminals, Full voltage non-reversing contactor

## General specifications



Product Name

Eaton XT IEC contactor

EAN

4015082771782

Product Height

1.5 in

Product Weight

.61729433 lb

Certifications

UL Listed CSA Certified IEC 60947 EN 60947

Catalog Number

XTCE025C01TD

Product Length/Depth

4 in

Product Width

3.5 in

Compliances

RoHS Compliant CE Marked

Catalog Notes

Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

## Product specifications

### Frame size

45 mm

### Contact configuration

1 NC

### Coil voltage

24-27 Vdc

### Series

XT IEC

### Type

Full voltage non-reversing contactor

### HP rating - max

2, 3, 5/ 7.5, 10, 15, 20 hp (1/3PH  
@115,200,230/200,230,460,575 V)

### Continuous ampere rating

25 A

### Terminals

Screw terminals

### Operation

Non-reversing

### Amperage Rating

25A

### Number Of Poles

Three-pole

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[XTCE\\_C 2D Drawing Xchange](#)

[XTCE\\_C AutoCAD 2D Footprint](#)

[XTCE\\_C 2D PDF](#)

[XTCE\\_C 3D Model Xchange](#)

### Specifications and datasheets

[Global Data Sheet - XTCE025C01TD](#)