

LA9GTS330

Star-Delta connection bar, for TeSys Giga
contactor LC1G630-800 (Line & Delta)/
LC1G265-500 (Star)



Main

Range	TeSys
Device short name	LA9G
Product or Component Type	Set of connections
Accessory / separate part category	Connection accessory
Electrical circuit type	Star-delta
Quantity per Set	Set of 1

Complementary

Poles description	3P
Product Compatibility	LC1G265...500
Range compatibility	TeSys Giga
Height	25.53 in (648.5 mm)
Width	6.93 in (176 mm)
Depth	3.46 in (88 mm)
Net Weight	22.88 lb(US) (10.38 kg)

Environment

Standards	EN/IEC 60947-4-1
Ambient Air Temperature for Storage	-76...176 °F (-60...80 °C)
Operating altitude	9842.52 ft (3000 m) without derating 5000 m with derating factor

Ordering and shipping details

Category	22328-TESYS GIGA ACCESSORIES
Discount Schedule	I12
GTIN	3606481916242
Returnability	No

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.72 in (19.6 cm)
Package 1 Width	12.05 in (30.6 cm)
Package 1 Length	20.55 in (52.2 cm)
Package 1 Weight	23.10 lb(US) (10.48 kg)
Unit Type of Package 2	S04
Number of Units in Package 2	1
Package 2 Height	11.81 in (30 cm)
Package 2 Width	15.75 in (40 cm)
Package 2 Length	23.62 in (60 cm)

Package 2 Weight	23.85 lb(US) (10.817 kg)
Package 3 Height	27.56 in (70.0 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes
Halogen content performance	Halogen free plastic parts product