



Main

Product or Component Type	Phase barrier
Accessory / separate part category	Installation accessories
Poles description	4P
Quantity per Set	Set of 3

Complementary

Product Compatibility	LC1G265...800
Height	0.08 in (2 mm)
Width	4.63 in (117.6 mm)
Depth	3.20 in (81.2 mm)
Net Weight	0.13 lb(US) (0.06 kg)
[Ui] Rated Insulation Voltage	1000 V

Environment

Pollution degree	3 IEC 60947-1
Ambient Air Temperature for Operation	-40...140 °F (-40...60 °C)
Ambient Air Temperature for Storage	-76...176 °F (-60...80 °C)
Operating altitude	9842.52 ft (3000 m) without derating 5000 m with derating factor
Standards	EN/IEC 60947-1 UL 60947-1 CSA C22.2 No 60947-1 GB/T 14048
Product certifications	ABS BV CB CCC CCS CUL CE DNV-GL EAC KC LROS (Lloyds register of shipping) RCM RINA RMRoS

Ordering and shipping details

Category	22328-TESYS GIGA ACCESSORIES
Discount Schedule	I12
GTIN	3606481915924
Nbr. of units in pkg.	1
Package weight(Lbs)	3.88 oz (110.0 g)
Returnability	No

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.79 in (2.0 cm)
Package 1 width	46.30 in (117.6 cm)
Package 1 Length	31.97 in (81.2 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	5
Package 2 Weight	19.40 oz (550.0 g)
Package 2 Height	5.91 in (15.0 cm)
Package 2 width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes
Halogen content performance	Halogen free plastic parts product