



Main

Device short name	LA9G
Product or Component Type	Spreader
Accessory / separate part category	Connection accessories
Range compatibility	TeSys LC1G TeSys LR9G
Poles description	4P
Quantity per Set	Set of 4

Complementary

Net Weight	0.55 lb(US) (0.25 kg)
Product Compatibility	LC1G115...225
Height	0.12 in (3 mm)
Width	2.07 in (52.5 mm)
Depth	3.15 in (80 mm)

Environment

Pollution degree	3 IEC 60947-1
Product Certifications	UL
Standards	EN/IEC 60947-1 UL 60947-1 CSA C22.2 No 60947-1 GB/T 14048
Ambient Air Temperature for Operation	-40...140 °F (-40...60 °C)
Ambient Air Temperature for Storage	-76...176 °F (-60...80 °C)
Operating altitude	9842.52 ft (3000 m) without derating 5000 m with derating factor

Ordering and shipping details

Category	22328-TESYS GIGA ACCESSORIES
Discount Schedule	I12
GTIN	3606481915856
Returnability	No

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.18 in (3.0 cm)
Package 1 Width	2.07 in (5.25 cm)
Package 1 Length	3.15 in (8.0 cm)
Package 1 Weight	10.44 oz (296.0 g)
Unit Type of Package 2	S02
Number of Units in Package 2	4

Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	41.76 oz (1184.0 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes
Halogen content performance	Halogen free plastic parts product