

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2155113121](#)
Status: **Active**
Overview: [PowerWize BMI High-Current Panel-to-Board/Busbar Interconnects](#)
Description: [PowerWize BMI 3.40mm, 2-circuit, Black Panel Mount Receptacle Housing in Bag](#)

Documents:

Drawing (PDF)	Test Summary 2155103000-TS-000 (PDF)
Product Specification 2155100003-PS-000 (PDF)	Datasheet (PDF)
Application Specification 2155101000-AS-000 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification 2155116121-PK-000 (PDF)	



Agency Certification

UL E29179

General

Product Family	Crimp Housings
Series	215511
Application	Panel-to-Board, Panel-to-Busbar, Power
Diameter	3.40mm
Overview	PowerWize BMI High-Current Panel-to-Board/Busbar Interconnects
Product Name	PowerWize BMI
Taxonomy	Connector Housings
UPC	195842380820

Physical

Circuits (maximum)	2
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	No
Material - Resin	PBT
Net Weight	8.460/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	Screws
Pitch - Mating Interface	12.50mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +125°C

Material Info

Reference - Drawing Numbers

Application Specification	2155101000-AS-000
Packaging Specification	2155116121-PK-000
Product Specification	2155100003-PS-000
Sales Drawing	2155113121-000
Test Summary	2155103000-TS-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[215511](#) Series

Mates With

3.40mm Male Header [2155103031](#) ,
[2155103241](#)

Use With

3.40mm Female Crimp Socket [2046083011](#)
(8 AWG), [2046083012](#) (10 AWG) . 3.40mm
Terminal Retention Housing [2155133001](#)