

BSR-44-BT BudStackRack

A revolutionary approach to 19" racks

- Ships unassembled for easy storage and shipment
- Incredible versatility as it can be used vertically or for 17.5" (10U) Panel Space or used horizontally for 21.0" (12U) Panel Space
- Can be used individually or as a stacked and connected together rack



Ordering Information

Part Number	Description	External Dimensions		Weight lb
		W x H x D		
		17.5" (10U) Panel Space	21.0" (12U) Panel Space	
BSR-44-BT	Complete Cabinet Rack Kit including all components needed for a stand-alone unit or for connecting multiple units	19.0" x 21.0" x 24.5"	19.0" x 24.5" x 21.0"	12.00

BudStackRack

THE BUDSTACKRACK CAN ALSO BE STACKED UP TO 3 UNITS HIGH USING EITHER PANEL SPACE OPTION

Sample Stacking using 17.5" Panel Space	Description	External size (W x H x D)		Weight lb
		17.5" (10U)	21.0" (12U)	
	Double Stacked	19.0" x 42.0" x 24.5"	19.0" x 49.0" x 21.0"	24.00
		Maximum Open Panel Space (A)		
		38.5" (22U)	42.0" (24U)	
	Tripple Stacked	19.0" x 63.0" x 24.5"	19.0 x 73.5" x 21.0"	36.00
		Maximum Open Panel Space (A)		
		59.5" (34U)	70.0" (40U)	

Benefits and Features

- Ships flat in a single carton (18 lb. shipping weight with dimensions 28" x 22" x 2")
- Ships unassembled with all necessary components and hardware. Quick and easy assembly with a #3 Philips screw driver in under 15 minutes
- 16 GA galvanized steel with black textured Powder
- Can be used either horizontally (17.5" panel space with 24.5" depth) or vertically (21.0" panel space with 21" depth)
- EIA spaced mounting holes incorporated into the front, back top and bottom for flexible component mounting
- Multiple units can easily be stacked together and attached vertically to create an uninterrupted panel space
- When stacked the user can gain 1 to 2 additional U mounting holes in the front where cross beams are omitted
- Can also be daisy-chained horizontally to create an add-a-rack situation for cross rack wiring
- Open design allows for maximum air flow
- Additional adjustable component mounting brackets are included for equipment support
- 300 lb. max weight limit for fully supported (4 points) 19" EIA rail mounted equipment (75" max height Included Accessory brackets can provide additional support for all accessories

BudStackRack

Accessories

This unit can be used with all of Bud's EIA rail mounted 19" Racks & Cabinet Accessories below is a partial list:

- 19-inch Rack Fan Tray with 3 Fans — FT-1973
- 19-inch Rack Fan Tray Assembly with 6 Fans and Digital Temperature Controller — FT-1986
- Equipment Shelf-Open Rack-Non-Ventilated 17.62 x 20 inches — SA-1750-BT
- Equipment Shelf-Open Rack-Non-Ventilated 17.62 x 20 inches — SA-1752-BT
- Adjustable Shelf-Open Rack 17.62 x 20 inches — SA-1279-BT
- Adjustable Shelf-Open Rack, 17.62 x 16 inches — SA-1278-BT
- Rackmount Power Outlet Strip — POS-194-S
- Rackmount Power Outlet Strip — POS-195-S
- Open Rack Monitor Shelf 19 x 19 inches — SA-1796-BT
- Adjustable Shelf Double Rack — SH-8-96
- Adjusting Brackets — AB-8089
- Rear Mounting Bracket — MB-14273

Applications

- All 19" rack EIA mount applications

Related Products

- Cabinet Racks
- Equipment that requires to be rack mounted
- Power supplies / Amplifiers

Key Customer Contacts

- Design Engineers
- Installation Designers / Managers
- Manufacturing Engineers

Questions to Ask

- Does the equipment need to be rack mounted?
- Do you have challengers maneuvering or storing cabinet racks within your facility?
- Would it be helpful to receive a rack that is knocked down?
- Would you like to reduce your freight costs?
- Do you want the flexibility to use a rack as a table top unit or connected as part of a cabinet rack?
- Do you need flexibility and multiple mounting options from the rack?

Availability

In Stock

BudStackRack