# **Strain Relief Bars**



### specifications

Strain relief bars shall consist of a metal bar that mounts to the rear of a standard EIA 19" rack to support a minimum of 24 cables exiting from the back of a patch panel. Cables shall be secured with integrated adjustable clips or hook and loop strips. Optional quick release brackets shall provide an easy way to remove the strain relief bar without the use of tools.



Mounting options:	All strain relief bars mount to standard EA 19" racks, or a standard 23" rack using an optional extender bracket	
Packaging:	#12-24 screws included SRBS19BL-XY includes 10 bars per package	

DC

 $\bigcirc$ 

### key features and benefits

Optional quick release brackets:	Enables strain relief bars to be removed and re-installed without the use of tools	
Deep strain relief bars:	Offer additional cable support and management, ideal for heavier cables; extend 5"-7"	
Quick removal:	oval: Select bars can be easily removed for easier access to connections	
SRBWCY Integrated adjustable clips:	12 clips provide enhanced cable management; organize cables individually for optimum finished appearance; accommodates multiple sizes and shapes of copper, fiber and coaxial cables for a wide variety of applications (cable diameter: 0.17"-0.33", 4.3mm-8.4mm); includes easy-release mounting feature	
SRBM19BLY Built-in cascade:		
Raised tie mounts:	Allows cables to be secured together with six enclosed ties	

### applications

Strain relief bars are used to support and manage cables in telecommunication rooms. Panduit offers a full line of strain relief bars to fit a variety of applications, offering end users the flexibility, convenience, and ability to support up to 72 cables. Strain relief bars can be used with standard 19" rack mountable patch panels and can also be mounted to 23" racks using optional extender brackets. Each bar occupies 1/3 to 2/3 of a rack space. Multi-depth bars are designed for installations that require additional features to support, organize, and secure heavier cables. Optional quick release brackets mount to a rack or behind a patch panel allowing the strain relief bar to be removed quickly.


	Strain Relief Bars with Cable Management and Easy Release Features					
	With clips:	SRBWCY				
	With integrated tie mounts:	SRBM19BLY				
	Strain Relief Bars					
	Straight:	SRBS19BL-XY				
	2" offset:	SRB19BLY				
•	5" offset (inward mounting*):	SRB19D5BL				
-	7" offset (inward mounting*):	SRB19D7BL				
	7" offset multi-depth:	SRB19MDBL				
•	Quick Release Brackets					
	Set of two:	SRBBRKT				
	Patch Panels					
•	Strain relief bars are compatible with all patch panels. See www.panduit.com for the complete selection.					
	Tak-Ty® Hook & Loop (	Cable Strip Tie				
-	15'L (4.6m), .75"W (19.1mm):	HLS-15R0				
	Ultra-Cinch <sup>™</sup> Hook & L	oop Ties				
_	3" (76mm) max. bundle diameter:	UCT3S-X0				
	<b>Optional Extender Bra</b>	ckets				
	1 RU:	PEB1				
	2 RU:	PEB2				

\*Bars with inward mounting feature require

19.75" clearance between rails or cabinet walls.

#### www.panduit.com

## **Strain Relief Bars**



Dimensions are in inches. [Dimensions in brackets are metric].

## **Strain Relief Bars**

## features and benefits at a glance

Part Number	Density	Feature	Quick Removal Feature	
SRBWCY	Standard	Adjustable clips	Yes	
SRBM19BLY		Hook and Loop tie mounts		
SRB19D7BL	High Density	7" deep		
SRB19MDBL		7" multi-depth		
SRB19BLY		2" offset	N/A	
SRB19D5BL	Standard	5" deep		
SRBS19BL-XY		Straight		

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty



For more information Visit us at www.panduit.com Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300 © 2022 Panduit Corp. ALL RIGHTS RESERVED. Printed in the U.S.A. NCSP44--WW-ENG 4/2022