

## Adjustable Depth Wall Rack with Shelf *APBS Series*

Rugged 100 lbs (45 kg) Weight Capacity

### Features



- Available in 4U and 8U mounting heights. Both sizes include 3.5" (2U) of space for non-rack mounting equipment.
- A twelve (12) inch depth accessory shelf is included.
- The rails vary in depth from 12" to 18" with ease, eliminating the need to disassemble the entire rack.
- Multiple tie points for cable management and rear cable access.
- The knockdown design allows for easy handling, lower freight costs, and better shipping protection.


### Specifications



- Constructed in 14-gauge steel.
- The 14-gauge steel mounting rails are threaded 10-32 and contain rack unit indicators.
  - **SCREW1032-25**, 25-pack of 10-32 mounting hardware included.
- 100 lbs (45 kg) **load rating**.
- Finished in RAL9005 black powder paint.
- TAA compliant for GSA Schedule purchases.
- RoHS Compliant.
- Manufactured in North America within an ISO 9001:2015 certified facility.

### Accessories

- Universal Rack Shelf
- Rack Panels
- 10-32 Mounting Hardware
- Cable Managers
- Hook and Loop Roll
- PDUs and Outlet Strips





Part No.	Overall Dimensions		Rack	Mounting Dimensions			
	Height	Width		Height	Width	Min Depth	Max Depth
APBS194UBK	10.54	19.25	4U	7.00	19.00	12.00	18.00
APBS198UBK	17.46	19.25	8U	14.00	19.00	12.00	18.00

What's Inside the Box

Qty Included	Description	Replacement Part No.
1	Rear wall-mounting section	
1	Left side section	
1	Right side section	
2	Sliding Rails	
1	Shelf/Cover	
25	10-32 x 0.75in Rack Mounting Screws	SCREW1032-25
10	10-32 x 3/8 Assembly hardware	
1	Assembly Instructions	

Tags: Hub-Shelf, Hub Shelf, knock-down, knock down, HA8UWBS, HA4UWBS

Data subject to change without notice