



## METAL PRESSURE CLIP, 16 CABLE, 0.28" HOLE

### CATALOG NUMBER

**PKM16H6**



### FEATURES

Ideal for smaller runs of cables

Flexible clip retains shape and allows for cables to be inserted after installation

Rounded edges help prevent cable damage

Cables are neatly installed providing a consistent and professional appearance

Low profile allows for installations in tight spaces

### PRODUCT ATTRIBUTES

Material: Spring Steel

Finish: nVent CADDY Armour

Cable Capacity: 16

Diameter: 0.390" Max

Hole Size: 0.280"


Length: 9 1/4"

### ADDITIONAL PRODUCT DETAILS

Supports cable diameters up to 1/2" (13 mm) when installed with a standard 1/4" (6 mm) washer.

## DIAGRAMS

---



## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**