



LG 32LQ631C TV 81.3 cm (32") Full HD Smart TV Wi-Fi Black

Brand : LG

Product code: 32LQ631C

Product name : 32LQ631C

- Full-HD resolution – For Sharp Images
- Google Assistant and Amazon Alexa & Alexa lite built in
- Dolby Audio™ - A movie-like sound experience
- USB Connection – Enjoy more content on your TV
- Simple Yet Sophisticated Design

LG 32LQ631C TV 81.3 cm (32") Full HD Smart TV Wi-Fi Black

LG 32LQ631C. Display diagonal: 81.3 cm (32"), Display resolution: 1920 x 1080 pixels, HD type: Full HD, Display technology: LCD, Screen shape: Flat, LED backlighting type: Direct-LED BLU. Smart TV. Native aspect ratio: 16:9. Digital signal format system: DVB-C, DVB-S, DVB-S2, DVB-T, DVB-T2. Wi-Fi, Ethernet LAN. Product colour: Black



Display		Ports & interfaces	
Display diagonal *	81.3 cm (32")	Audio Return Channel (ARC)	✓
HD type *	Full HD	Ethernet LAN (RJ-45) ports *	1
Display technology *	LCD	USB 2.0 ports quantity *	2
LED backlighting type	Direct-LED BLU	Composite video in	1
Screen shape *	Flat	Digital audio optical out	1
Native aspect ratio *	16:9	RF ports quantity	2
Supported graphics resolutions	1920 x 1080 (HD 1080)	Common interface (CI) *	✓
Native refresh rate	60 Hz	HDMI ports quantity *	2
Display resolution *	1920 x 1080 pixels	PC in (D-Sub) *	✗
TV tuner		Management features	
Tuner type *	Analog & digital	On Screen Display (OSD)	✓
Digital signal format system *	DVB-C, DVB-S, DVB-S2, DVB-T, DVB-T2	Number of OSD languages	36
Smart TV		Works with Amazon Alexa	✓
		Works with the Google Assistant	✓
		Power	
		Energy efficiency class (SDR) *	G
Operating system installed *	Web OS	Energy consumption (SDR) per 1000 hours *	33 kWh
Operating system version	WebOS22	Power consumption (standby) *	0.5 W
Timeshift	✓	AC input voltage	100 - 240 V
Apple AirPlay 2 support	✓	AC input frequency	50/60 Hz
Audio		Energy saving mode	✓
Number of speakers *	2	Energy efficiency scale	A to G
RMS rated power *	10 W	Supplier features	
Audio decoders	DTS	Country of origin	South Korea
Sound modes	Clear Voice III	Weight & dimensions	
Network		Width (with stand)	812 mm
Wi-Fi *	✓	Depth (with stand)	142 mm
Ethernet LAN *	✓	Height (with stand)	510 mm
Wi-Fi standards	Wi-Fi 5 (802.11ac)	Weight (with stand)	4.7 kg
Bluetooth *	✓	Width (without stand)	73.6 cm
Bluetooth version	5.0	Depth (without stand)	18 cm
Bluetooth Low Energy (BLE)	✓	Height (without stand)	46.4 cm
Web browser	✓	Weight (without stand)	4.65 kg
Design			
On/off switch	✓		

Design		Weight & dimensions	
VESA mounting *	✓	Stand width	60.6 cm
Panel mounting interface	200 x 200 mm	Packaging data	
Product colour *	Black	Desktop stand	✓
Performance		Remote control included	✓
High Dynamic Range (HDR) supported *	✓	Remote control type	L-Con
High Dynamic Range (HDR) technology	High Dynamic Range 10 Pro (HDR10 Pro), Hybrid Log-Gamma (HLG)	Package width	812 mm
Teletext function	✓	Package depth	142 mm
Teletext	2000 pages	Package height	510 mm
Subtitles function	✓	Package weight	5.9 kg
Audio formats supported	AAC, AC3, DTS, EAC3, HE-AAC, MP2, MP3, PCM, WMA, apt-X	Package type	Box
Noise reduction *	✗	Logistics data	
Video upscaling	✓	Harmonized System (HS) code	85287280
Ports & interfaces		Other features	
HDMI version	1.4	HDMI	✓



8806091662897

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 02-MAR-2023. Prints or copies of Information are only valid on the printed Publication date