

YourHome Festoon String

YourHome Festoon String UK

0086323



Product features

- An outdoor festoon with 12 E27 lamp holders, sold without ToLEDo Retro Chroma A60 lamps, - High quality rubber cables and custom Sylvania tooling design, -Integrated suspension hooks on every lampholder, - Through-wiring feature allows extension up to 30 chains (up to 273m), - IP54 water/dust/dirt resistant, - Independently tested for quality and safety (CE/UKCA), - Applications include: gardens, theatres, music festivals, hotels and pub garden illumination



PRODUCT OVERVIEW

Product name	YourHome Festoon String UK
Technology	SPG
General application	Hospitality, Residential & Consumer, Retail, SPG
ETIM Class	EC002761
Warranty	1 year
Light colour	N/A
Photobiological Risk Group	Not applicable
Electrical protection	Class II
Dimmable	No
IP rating	IP54
IK rating	IK00
Product EAN number	5410288863238
Dimming method	N/A

DATA TABLE

General data

Product name	YourHome Festoon String UK
Technology	SPG
General application	Hospitality, Residential & Consumer, Retail, SPG
ETIM Class	EC002761
Warranty	1 year

Optical data

Light colour	N/A
Photobiological Risk Group	Not applicable

Electrical data

Mains voltage (V)	220-240V
Electrical protection	Class II
Dimmable	No
Nominal Frequency (Hz)	50/60Hz

YourHome Festoon String

YourHome Festoon String UK
0086323

Physical data

IP rating	IP54
IK rating	IK00
Nominal Product Length (mm)	12000
Weight (kg)	1.9

Packaging

Single packaging type	Carton
Product EAN number	5410288863238
Packaging single length / height (cm)	21.0
Packaging single width (cm)	15.0
Packaging single depth (cm)	29.0
DUN14 (outer)	05410288863238
Units per outer package	100
Packaging outer length / height (cm)	120.0
Packaging outer width (cm)	80.0
Packaging outer depth (cm)	116.0

Safety data

Safety message	Not suitable for household
----------------	----------------------------