



## **NAUSB-W**

Reversible USB 2.0 gender changer (type A and B), Nickel D-housing

Due to the rising digitisation the interface problems between audio/video networks, IT equipment, MP3 camcorders, etc. increase. A rugged solution is needed.

Neutrik's reversible USB gender changer, mounted in the standardized D-shape housing, and the rugged patch cables solve this problem.

## **Features & Benefits**

- Ideal for audio networking and integration of computerbased equipment into audio systems
- USB 2.0 gender changer type A-B (B-A)
- Universally accepted standard D-shape housing
- IP65 ingress protection in mated condition with NKUSB-\* and SCDP-\* sealing gasket
- Reversible insert offering type A or B on front or rear end



## **Technical Information**

Product	
Title	NAUSB-W
Connection Type	Adapter
Gender	female

Mechanical	
Wiresize	
Mounting direction	Front mounting
Chassis shape	D
Lifetime	> 1000 mating cycles

Material	
Contact plating	Au
Contacts	Brass (CuZn39Pb3)
Insert	PBTP 15 % GR
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Nickel

Environmental	
Flammability	UL 94 V-0
Standard compliance	USB 2.0 specifications
Temperature range	-25 °C to +85 °C