



#### TECHNICAL INFORMATION

Shape:	Round
Input Power:	AC:200-240V, 50Hz
Unit Color:	Polished Brass
Body Type:	Pressed Steel
Cutting Size:	68mm
Dimension:	85x90.3mm



#### CANLESS FITTINGS IP20 | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

#### FEATURES

- Twist & lock fire rated canless fitting designed with GU10 base(\*lamp not included)
- Fire-rated to resistance of 30,60,90 Mins
- Elegant Polished Brass color finish
- Easy connection - Quick Connector included
- Insulation Cover available(\*not included)
- Spring clips for safer installation and easy maintenance
- IP20 rated protection
- Suitable for residential and commercial installations



#### LISTING DETAILS

Ean Code: 3800157699686

#### PACKAGING

Gross Weight (Kgs):	0.21
Unit CBM:	0.00089
Dimension:	85x90.3mm

#### MASTER BOX PACKAGING

Box Qty:	20
Length (Box) mm:	105
Width (Box) mm:	89
Height (Box) mm:	78