

Product data sheet

Specifications

SQUARE D

Green Premium™



INDUSTRIAL CONTROL TRANSFORMER 50VA MULTI-VOLTAGE WITH 610mm/24INCH LEADS

9070EL1D9

Main

Product or component type	Industrial Control Transformer
Range of product	EL

Complementary

Network number of phases	1 phase
Rated power in VA	50 VA
Primary voltage	480 V 440 V 460 V
Secondary voltage	115 V 120 V 110 V
Temperature rise	55 °C
Electrical connection	Screw clamp terminals
Connector type	Lead 2001.31 ft (610 m)

Environment

Product certifications	UL listed CSA CE
NEMA degree of protection	Not rated (open device)
Insulation temperature	221 °F (105 °C)

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.70 in (9.398 cm)
Package 1 Width	4.00 in (10.16 cm)
Package 1 Length	4.10 in (10.414 cm)
Package 1 Weight	2.61 lb(US) (1.184 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Recommended replacement(s)