

INSTALLATION INSTRUCTIONS

PRODUCT: IGNIS PLUS DIE-CAST FIRE RATED GU10 DOWNLIGHTS PRODUCT CODES: IGP/FB, IGP/FC, IGP/FSC, IGP/FW, IGP/TB, IGP/ TC, IGP/TSC, IGP/TW, IGP/65B, IGP/65C, IGP/65SC, IGP/65W

IMPORTANT NOTES -

- ALWAYS SWITCH OFF THE MAINS SUPPLY BEFORE SERVICING FITTING OR REPLACING LAMPS. FOLLOW INSTALLATION STEPS 5A/5B TO 7A/7B WHEN REPLACING LAMPS
- ALWAYS CHECK THE LAMP IS CORRECT FOR THE APPLICATION INCLUDING ITS VOLTAGE AND WATTAGE - 230V & MAX. 50W.
- SPECIAL ATTENTION SHOULD BE PAID TO ANY INSTALLATIONS WITH LOW CEILING VOIDS.
- NEVER EXCEED THE MAXIMUM LAMP WATTAGE 50W.
- ENSURE THE LAMP IS CORRECTLY LOCATED IN THE LAMPHOLDER.
- WE RECOMMEND THE USE OF LED LAMPS WITH THIS LUMINAIRE. PLEASE USE RED ARROW LED GU10 RANGE FOR THE BEST RESULTS.

GUARANTEE

This product is guaranteed for a period of 1 years from the date of purchase. The guarantee is invalid in the case of improper use, tampering, removal of the Q.C. date label, installation in an improper working environment or installation not according to the current edition of the I.E.E. Wiring Regulations (BS7671).

The guarantee is also invalidated if the luminaire has been insulation tested. Should this product fail during the guarantee period it will be replaced free of charge, subject to correct installation and return of the faulty unit. We do not accept responsibility for any installation costs associated with the replacement of this product. Your statutory rights are not affected. We reserve the right to alter specifications without prior notice.

MAINTENANCE

- This fitting will require routine cleaning if used in adverse (dust, paint, welding, oils etc) environments. Do not use solvents, aggressive detergents or abrasives.
- When this fitting comes to the end of it's life or you choose to replace it, please do not dispose of it with your normal household waste. Please recycle where the facilities exist, check with your local authority or retailer for suitable options.







INSTALLATION INSTRUCTIONS

PRODUCT: IGNIS PLUS DIE-CAST FIRE RATED GU10 DOWNLIGHTS PRODUCT CODES: IGP/FB, IGP/FC, IGP/FSC, IGP/FW, IGP/TB, IGP/TC, IGP/TSC, IGP/TW, IGP/65B, IGP/65C, IGP/65SC, IGP/65W

BOX CONTENTS -

1 x IGNIS PLUS FIRE RATED **GU10 DOWNLIGHT**







Fixed & Tilt

IP65 version only

Dimensions:	Fixed: L95 x Ø86mm. Cut out: Ø: 75mm Tilt: L95 x Ø100mm. Cut out: Ø: 90mm IP65: L105 x Ø86mm. Cut out: Ø: 75mm
Material:	Die-Cast Aluminium
Included:	Fast Fit Terminal Block with Heavy Duty Loop In/ Loop Out Lever Type Connectors Steel Ceiling Fixing Springs




BEFORE INSTALLATION -

WE RECOMMEND THAT A SAMPLE HOLE BE CUT IN SOME SCRAP MATERIAL TO FAMILIARISE YOURSELF WITH THE INSTALLATION. ONCE YOU ARE COMPLETELY SATISFIED: LOCATE THE AREAS SUITABLE FOR INSTALLING THESE LUMINAIRES. CUT A SUITABLE HOLE IN THE CEILING AND ENSURE SUFFICIENT CEILING VOID WITHOUT INFRINGING ON JOISTS, WATER PIPES OR ELECTRICAL CABLES,

CONNECT THIS PRODUCT TO A 230V SUPPLY.

FIT THIS PRODUCT AS ILLUSTRATED IN THE STEPS ON THE FOLLOWING PAGES. THIS PRODUCT IS A CLASS 1 ELECTRICAL DEVICE.

DO NOT INSTALL THIS PRODUCT INTO NEW PLASTER OR DAMP AREAS



SAFETY WARNING



- The installation should be carried out by a qualified electrician in compliance with the current edition of the IEE Wiring Regulations.
- Prior to installation, carry out the necessary risk assessment considering the people who could be at risk, the level of risk and the precautions required to control the risk
- Ensure that the circuit supply is
- isolated either by the circuit supply fuse being removed or the applicable circuit breaker being turned off before installation or any maintenance.
- Check the total load on the circuit ensuring the luminaire does not exceed the rating of the circuit cable, fuse or circuit breaker.
- · Long-term use and voltage fluctuations can reduce the life span of the fitting.
- If the fitting incorporates control gear, ensure careful sizing to avoid instances of nuisance tripping of the protective device used in the installation.
- Follow the provided installation instructions, using the fixings supplied or recommended.
- · Keep out of reach of children





INSTALLATION INSTRUCTIONS

PRODUCT: IGNIS PLUS DIE-CAST FIRE RATED GU10 DOWNLIGHTS PRODUCT CODES: IGP/FB, IGP/FC, IGP/FSC, IGP/FW, IGP/TB, IGP/ TC, IGP/TSC, IGP/TW, IGP/65B, IGP/65C, IGP/65SC, IGP/65W


INSTALLATION INSTRUCTIONS -


- 1. CUT OUT A HOLE IN THE CEILING TO THE APPROPRIATE SIZE (SHOWN IN TABLE ON PREVIOUS PAGE). FEED THE POWER SUPPLY CABLE THROUGH THE HOLE.
- 2. CONNECT THE POWER SUPPLY TO THE PUSH-FIT CONNECTORS INSIDE THE TERMINAL BLOCK: HEAVY DUTY LOOP IN / LOOP OUT DOUBLE INSULATION LIVE, NUETRAL & EARTH PROVISION PROVIDED.
- 3. LOCATE THE TERMINAL BLOCK ONTO THE BRACKET ON THE DOWNLIGHT.
- 4. PUSH THE CEILING SPRINGS UP & OFFER THE DOWNLIGHT INTO THE CEILING CUT-OUT. RELEASE SPRINGS WHEN THE DOWNLIGHT IS LOCATED IN THE HOLE AND GENTLY PUSH THE FITTING UP FLUSH TO THE CEILING.





redarrowelectrical.com







INSTALLATION INSTRUCTIONS

PRODUCT: IGNIS PLUS DIE-CAST FIRE RATED GU10 DOWNLIGHTS PRODUCT CODES: IGP/FB, IGP/FC, IGP/FSC, IGP/FW, IGP/TB, IGP/ TC, IGP/TSC, IGP/TW, IGP/65B, IGP/65C, IGP/65SC, IGP/65W

INSTALLATION INSTRUCTIONS (CONT'D) -

- **5A.** FIXED & TILT TWIST THE INNER BEZEL ANTICLOCKWISE TO REMOVE IT FROM THE DOWNLIGHT.
- **5B.** IP65 ONLY TWIST THE BEZEL ANTICLOCKWISE TO REMOVE IT FROM THE DOWNLIGHT.
- **6.** LOCATE THE LAMP INTO THE SPRING CLIP ON THE REAR OF THE INNER BEZEL. CONNECT THE LAMP TO THE LAMPHOLDER, TWISTING CLOCKWISE UNTIL A POSITIVE LOCKING CONNECTION IS MADE.
- 7A. FIXED & TILT PUSH THE LAMP & BEZEL INTO THE DOWNLIGHT & TWIST THE INNER BEZEL CLOCKWISE TO LOCK BACK INTO POSITION.
- **7B.** IP65 ONLY PUSH THE LAMP & BEZEL INTO THE DOWNLIGHT & TWIST CLOCKWISE TO LOCK BACK INTO POSITION.

