

Datasheet – Panasonic EH-NA67

The Panasonic nanoe Hair Dryer is designed to prevent hair damage while protecting your scalp.

This hair dryer features Panasonic's nanoe technology. The innovative ionic system is anti-static and improves visible shine by conditioning hair to lock in moisture, maintaining approximately 1,000 times more moisture than other hair dryers. This hair tool allows moisture to penetrate deep into each strand to ensure an optimal balance. Worried about heat damage? The Panasonic nanoe™ reduces and minimises damage from your brush and hair accessories and keeps the cuticle on the surface in good condition.

The hair dryer comes with a unique technology oscillating nozzle for gentle yet fast drying and also includes a concentrator nozzle for controlled drying. This attachment disperses hot air from left to right to prevent hot spots and emits both strong and weak airflows which separates hair strands for Turbo drying power. The unique blower mechanism dries your hair from the roots to maintain hair and scalp health for both long hair and short hair.

The Panasonic diffuser attachment helps you gently dry thick hair or curls without losing volume or definition. The diffuser reduces frizz and dryness for silky, smooth styling. Airflow moves across the hair evenly to give you glossy hair while simultaneously protecting your scalp and improving shine.

With a choice of 3 speed settings and 4 temperature settings, you can control the speed and temperature and match the condition of your hair or styling needs and preferences. Set your style with the cool-shot button, which maintains your style for longer.

The advanced nanoe™ hair dryer delivers salon-quality results. Enjoy healthy, flawless shine, with less heat damage, additional moisture, dryness prevention, and visibly shiny hair.

Designed for family comfort and style

Avoiding hot spots when drying a child's hair can be quite the challenge. Use our unique oscillating quick-dry nozzle that distributes airflow around the hair for less hot spots and maximum comfort.

Hello shine, goodbye frizz

Thanks to nanoe technology, nano-sized water particles penetrate your hair cuticles to restore moisture balance, reducing frizz and revealing your natural shine from root to tip. *Test results by Intertek and Certification Ltd.

Oscillating nozzle

When the nozzle is pulled out, it uses a gentle motion to automatically prevent hot spots on your hair and scalp whilst providing quick drying.

Your style, your way

Tailor your look using our concentrator nozzle that's ideal for precision drying and styling as it focuses and concentrates the airflow.

Embrace your curls

Our diffuser attachment disperses the flow of air more liberally, adding volume from the roots, and defines curly and wavy hair.

4 temp. settings / 3 speeds

Everyone's hair is unique, that's why we've included four temperature settings and three speeds to match the condition and style of your hair.

Specifications

- Wattage: 2000W (at 240V)
- Ion: nanoe™
- Cool-Shot button: Yes
- Speed: 3 settings
- Temperature: 4 settings
- Foldable: No
- Attachments: Oscillating quick dry nozzle, Diffuser, Concentrator
- Body Size (W x H x D): 90 x 230 x 200(w/o nozzle) mm
- Weight: Approx. 547 g(w/o cord, nozzle)