

Datasheet - Panasonic ES-LL21

Sharp & Smooth Finish

The acute 30 degree cutting edge of the inner blades enables an incredibly close shave. Driven by a high-speed motor, the blades cut smoothly through the toughest beards.

Efficient coverage and maximum comfort thanks to the multi-fit arch and floating head, you can enjoy a smooth, close shave even in areas where stray hairs are hard to catch, such as on your cheeks and under your chin.

Shaving Sensor Technology

Shaving Sensor Technology recognises differences in density of your beard as you shave; boosting power where your beard growth is heavy, and reducing power where it is thin.

This reduces the burden on your skin minimising skin irritation, whilst providing optimal shaving results.

Pop-up Trimmer

Pops up with a simple press of the thumb and is ideal for cutting missed stray hairs on your neck and grooming sideburns.

Washable for Easy Maintenance

Waterproof design for easy and hygienic maintenance. You can rinse the shaver under running water.

Ergonomic Curve Design

Ergonomically designed, this shaver enables comfortable shaving in the most natural position, without placing strain on the elbow or wrist.

LED Display

LED indicator displays battery charging status and remaining battery capacity.

- 3-blade shaver that's powerful yet gentle to skin. Panasonic ES-LL21's linear motor delivers cutting performances even on the thickest beards; whilst the shaving sensor technology takes care of your skin and minimises irritation. 1
- 3,000 CPM linear motor provides a smooth, clean shave, with no power loss or missed whiskers, even when shaving heavy beards.
- The acute 30 degrees cutting edge of the inner blades enables an incredibly close shave.
- Driven by a high-speed motor, the blades cut smoothly through the toughest beards. Panasonic ES-LL21's shaving sensor technology recognises differences in the density of your beard as you shave; boosting power where your beard growth is heavy, and reducing power where it is thin.
- Reduces the burden on your skin minimising skin irritation, while providing optimal shaving results Thanks to the multi-fit arch and floating head, you can enjoy a smooth, close shave even in areas where stray hairs are hard to catch, such as on your cheeks and under your chin Pop-up trimmer (which pops up with a simple press of your thumb) is ideal for cutting missed stray hairs on your neck and grooming sideburns Wet/dry operation -

- Enjoy the convenience of dry operation or use with foam or gel for pampering silky-smooth shave Washable -
- Waterproof design for easy and hygienic maintenance. You can rise the shaver under running water Ergonomic designed unit enables shaving in the most natural position without placing strain on the elbow or wrist LED indicator display battery charging status and remaining battery capacity 1 hour charge for up to 50 minutes running time.

Specification

- Pop-up Trimmer: Yes
- Attachment: No
- Type of Motor Linear Motor Approx.: 13,000cpm
- Blade Type: 3-Blade
- Inner Blade: 30°Nano Polisehd Inner Blades
- Shaving Sensor(LED Indicator): Yes
- WET / DRY: Yes
- Charging Indicator: 2LED
- Charging Time: 1hour
- Operating Time: 50 min
- Power-supply voltage: 100-240 V
- Replacement Blade(Outer): WES9087P
- Replacement Blade(Inner): WES9068P
- Replacement Blade(Set): WES9013P
- Product dimensions (H x W x D): 15.5x 6.4 x 4.9 cm
- Body Weight: Approx.155g