

# **EVO-STIK Sticks Like Adhesive White**

# A HIGH STRENGTH, SINGLE PART, SMP POLYMER ADHESIVE

### Date: 20 July 2018

#### YOUR SMART ADVANTAGES

- Excellent adhesion and initial grab
- Can be used in all weather conditions
- Wide service temperature range of -40°C to +100°C

#### USES

EVO-STIK Sticks Like Adhesive White is a high performance, single component, moisture curing, Silyl Modified Polymer (SMP) based adhesive. It will bond most surfaces even if both are impervious and can be applied to damp or wet surfaces. EVO-STIK Sticks Like Adhesive White is low odour and cures to form a hard elastic rubber, with almost no shrinkage and no hazard; it does not contain any water or solvent, making it ideal for bonding foam polystyrene sheets.

EVO-STIK SticksLike Adhesive White bondstomost surfaces including wood, concrete, brick, plaster, glass, ceramics, metals, rigid pvc, grp insulation boards and foam polystyrene.

PRODUCT CHARACTERISTICS				
Colour	Warm white			
Form	Thixotropic paste			
Specific Gravity	1.5 approx.			
Composition	Moisture curing SMP Polymer system			
Product Code	30813033 C20 cartridge x 12			
Storage/Shelf Life	Store for up to 18 months from date of manufacture when stored in original, unopened packaging under dry conditions within the temperature range of +5°C to +25°C and out of direct sunlight. Protect from frost.			

## FactSheetNo.: TDS01641

TYPICAL PERFORMANCE DATA (Approx.)					
Service Temperature	-40°C to +100°C				
Coverage (approx.)	44 metres of 3mm diameter bead per C20 cartridge 14 metres of 5mm diameter bead per C20 cartridge				
Drying Times	Touch Dry: 30 to 40 minutes Cure Time: 24 hours depending on bead size and substrates being bonded				
Shore A Hardness	50 - 55				
Tensile Strength	1.5 – 1.8 MPa				
Resistances	Water: Excellent resistance Oil & Petrol: Good resistance Chemicals: Good resistance Abrasion: Good resistance				
Solvent For Cleaning Up	When wet: White spirit When dry: Mechanical removal e.g. cut, scrape, sand				

#### DIRECTIONS FOR USE

IMPORTANT: Before using EVO-STIK Sticks Like Adhesive White refer to the relevant Health & Safety Data Sheet, available at www.bostik.co.uk.

#### PREPARATION

 Surfaces must be sound, clean and free from any contaminants such as dust, oil, grease and any loose material. Damp surfaces must be checked for weak or loose material on the surface that the damp might hide.

Bostik Limited, Common Road, Stafford, ST16 3EH, UK. Tel: +44 (0) 1785 272625 <u>www.bostik.com/uk</u> Bostik, Evo-Stik & Sealocrete are registered trademarks of Bostik Ltd.

- 2. EVO-STIK Sticks Like Adhesive White should not be used on surfaces contaminated by bitumen. Not suitable for use in continuous submersion in water.
- 3. Cut off the dome at the top of the cartridge taking care not to damage the thread. Cut the nozzle to the desired width and angle and screw onto the cartridge.
- 4. Insert the cartridge into a cartridge gun and repeatedly squeeze the trigger until the adhesive appears.

#### **APPLICATION**

- 5. Apply parallel beads of adhesive to one of the surfaces, align and bring the surfaces together within 10 minutes.
- 6. Beads 5mm in diameter are generally sufficient. For close fitting surfaces the bead may be reduced to 3mm diameter.
- The degree of separation of the beads of EVO-STIK Sticks Like Adhesive White will depend upon the rigidity and weight of the panel, board or sign being bonded. If beads are separated by more than 200mm a perimeter bead should be applied.
- 8. For rigid sheets 100 150mm separation between beads is generally sufficient for high loading, but may be increased if the load is low (such as wallboards and foam polystyrene) where 200mm – 500mm is acceptable.
- For less rigid boards the separation may need to be quite small and it is important to choose the correct bead size.

#### CLEANING

- 10. Uncured product may be removed using cloths lightly dampened with white spirit, after carefully scraping off the bulk.
- 11. Cured product requires mechanical removal.

#### PRECAUTIONS IN USE

EVO-STIK Sticks Like Adhesive White will not bond Polyethylene, Polypropyleneor Teflon. It should not be used on surfaces contaminated with bitumen. EVO-STIK Sticks Like Adhesive White is not suitable for continuous submersion in water. EVO-STIK Sticks Like Adhesive White must not be used to bond mirrors if the mirror is backed with plastic safety film. Do not bond mirrors to painted surfaces, as the decorative finish will be unable to support the load.

For any application not covered please contact Technical Services on +44 (0)1785 272625 or visit www.bostik.co.uk for advice.

Recommendations and suggestions are for guidance only, since conditions of use are completely beyond our control.

For health and safety instruction, first aid measures and spillage and disposal instructions, see separate Health and

Safety Data Sheet for EVO-STIK Sticks Like Adhesive White, available at www.bostik.co.uk.

#### BOSTIK HOTLINE

Smart help +44 (0) 1785 272625

This disclaimer is issued by Bostik Limited ("the Company") and applies to the use of any products supplied by the Company ("the Products") displayed on this Technical Data Sheet ("TDS"). Please read this disclaimer carefully before using any of the Products. Using this TDS and/or the Product constitutes your acceptance of this disclaimer. Its contents shall prevail over any directions of use and any disclaimer and/or exclusion or limitation of liability of the Company which may appear on the packaging of the Products.

This disclaimer sets out the entire financial liability of the Company (including any liability for the acts or omissions of its employees, agents and sub-contractors) to any user of the Products ("Product User") in respect of any use made or resale by the Product User, of any of the Products in this TDS.

This disclaimer does not affect the Company's liability for death or personal injury arising from the Company's negligence in respect of the Products, nor its liability for fraud, or fraudulent misrepresentation, nor any other liability which cannot be excluded or limited under applicable law.

The Company's total liability however arising and whether caused by tort(including negligence and breach of statutory duty), breach of contract or otherwise, arising in connection with the use made or resale by the Product User of any of the Products in this TDS shall be limited to the price paid for the Product by the Product User.

The Company shall not be liable to the Product User for any pure economic loss, loss of profit, loss of business, depletion of goodwill or otherwise, in each case whether direct, indirect or consequential, or any claims (including in respect of personal injury insofar as not caused by the Company's negligence) for consequential compensation whatsoever (howsoever caused) which arise out of or in connection with the use made or resale by the Product User of any of the Products in this TDS.

The Company shall not be liable to the Product User in relation to any loss for any use which is inappropriate or use which is otherwise than in accordance with the relevant instructions for use of the Products in this TDS or on the Product. Product Users are advised to confirm the suitability of the Products by their own tests.

This TDS covers just one of a large range of products supplied by the Company.

Full information on these products and advice on application is freely available from our fully trained staff throughout the country. In addition, specialist technical advice is available from our Technical Services Department. This TDS supersedes all previous TDSs relating to the Products, and users of it must ensure that it is the current issue. Destroy all previous TDS, and if in any doubt, contact the Company, quoting the code number in the top right hand corner on the front of this document.

Sales	Tel: 0844 371 1192	Fax: 01785 241818	customer.service@bostik.com
Technical Advice	Tel: 0844 371 1197	Fax: 01785 272867	technical.service@bostik.com
Safety Data Sheets	Tel: 01785 272625	Fax: 01785 212962	<u>sds.box-eu@bostik.com</u>

Bostik Limited, Common Road, Stafford, ST16 3EH, UK. Tel:+44 (0) 1785 272625 www.bostik.com/uk Bostik, Evo-Stik & Sealocrete are registered trademarks of Bostik Ltd.