



infrastructure for a connected world

PRODUCT CHANGE NOTIFICATION

Product Category COPPER - CABLE - 1G **20230301-1**

Product Group BULK COPPER CABLE

ISSUE DATE: ☒ NA ☒ MEA ☒ LATAM ☒ AP-Mar-23

IMPACTED REGIONS: ☒ DISCONTINUATION

REASON FOR CHANGE: ☐ OTHER

DESCRIPTION OF CHANGE: (Required)

Parts are being discontinued in order to streamline the product offering. Thanks for your ongoing support.

Photos/Drawing (where applicable)

IMPACTED PART NUMBERS AND REPLACEMENT PART NUMBERS: (where applicable)

DATES: DISCONTINUATION AND NEW PRODUCT AVAILABILITY:

SCHEDULE FOR CHANGE	Year (YYYY)	Month (MM)	Day (DD)
New product sample availability date	2023	3	1
Old product discontinuation date*	2023	5	30

***Important:** A return material authorization (RMA) may be obtained for these affected part numbers and they may be returned up to 60 days after the product discontinuation announcement date if purchased within the last 18 months and subject to the return policy requirements outlined in Panduit's Authorized Distributor Policy. Please contact your local Panduit Customer Experience team if you have any questions.

CUSTOMER SERVICE CONTACTS

ASIA PACIFIC	AUSTRALIA: 1-800 7263848 AUS-CSVM@panduit.com	CHINA: 400-820-1900 CHN-CustomerService@panduit.com	HONG KONG: 800-965768 CHN-CustomerService@panduit.com
	INDIA: 000 800 6501844 (Fixed) 000 800 6500369 (Mobile) SGP-Customer_Service@panduit.com	INDONESIA: 001 803 65 7571 SGP-Customer_Service@panduit.com	JAPAN: +81-3-6863-6000 JPN-CS@panduit.com
	KOREA: 02-2182-7300 KOR-CustomerService@panduit.com	MALAYSIA 1800 801435 SGP-Customer_Service@panduit.com	SINGAPORE: 1-800-7263848 SGP-Customer_Service@panduit.com
	TAIWAN: 0080 165 1487 SGP-Customer_Service@panduit.com	THAILAND: 001-800-65-6385 SGP-Customer_Service@panduit.com	
LATIN AMERICA	BRAZIL 08000562613 (Toll Free) BRA-custservice@panduit.com	MEXICO: +52-33-37776000 x80520 01 800 360 86 00 (Toll Free) MEX-customerservice@panduit.com	OTHER LA COUNTRIES: Phone USA 1-708-532-1800 TP-CS-INTERNATIONAL@panduit.com
NORTH AMERICA	USA & CANADA: 1-800-777-3300 cs@panduit.com	EMEA	EMEA: +44 208 6017219 EMEA-CustomerServices@panduit.com

IMPACTED PART NUMBER(s)	Replacement Part 1	Replacement Part 2
PUP6C04BU-F	PUP6C04BU-WZ	PUP6C04BU-WLPZ
PUP6C04IG-F	PUP6C04IG-WZ	PUP6C04IG-WLPZ
PUP6C04GR-F	PUP6C04GR-WZ	PUP6C04GR-WLPZ
PUP6C04OR-F	PUP6C04OR-WZ	PUP6C04OR-WLPZ
PUP6C04VL-F	PUP6C04VL-WZ	PUP6C04VL-WLPZ
PUP6C04YL-F	PUP6C04YL-WZ	PUP6C04YL-WLPZ
PUP6C04BL-W-S	PUP6C04BL-WZ	PUP6C04BL-WLPZ
PUP6C04IG-W-S	PUP6C04IG-WZ	PUP6C04IG-WLPZ
PUP6C04GR-W-S	PUP6C04GR-WZ	PUP6C04GR-WLPZ
PUP6C04VL-W-S	PUP6C04VL-WZ	PUP6C04VL-WLPZ
PUP6C04YL-W-S	PUP6C04YL-WZ	PUP6C04YL-WLPZ
PUP6C04BL-ULP	PUP6C04BL-WLPZ	PUP6C04BL-WZ
PUP6C04IG-ULP	PUP6C04IG-WLPZ	PUP6C04IG-WZ
PUP6C04GR-ULP	PUP6C04GR-WLPZ	PUP6C04GR-WZ
PUP6C04RD-ULP	PUP6C04RD-WLPZ	PUP6C04RD-WZ
PUP6C04VL-ULP	PUP6C04VL-WLPZ	PUP6C04VL-WZ
PUP6C04WH-ULP	PUP6C04WH-WLPZ	PUP6C04WH-WZ
PUP6004BL-ULP	PUP6004BL-ULPZ	-
PUP6004BU-ULP	PUP6004BU-ULPZ	-
PUP6004IG-ULP	PUP6004IG-ULPZ	-
PUP6004GR-ULP	PUP6004GR-ULPZ	-
PUP6004RD-ULP	PUP6004RD-ULPZ	-
PUP6004OR-ULP	PUP6004OR-ULPZ	-
PUP6004VL-ULP	PUP6004VL-ULPZ	-
PUP6004YL-ULP	PUP6004YL-ULPZ	-
PUP6004BU-WLP-S	PUP6004BU-WLPZ	-
PUP6004IG-WLP-S	PUP6004IG-WLPZ	-
PUP6004GR-WLP-S	PUP6004GR-WLPZ	-
PUP6004WH-WLP-S	PUP6004RD-WLPZ	-

PUP6004YL-WLP-S	PUP6004OR-WLPZ	-
PUP6504BL-UY	PUP6004BL-WLPZ	PUP6XHD04BL-G
PUP6504BU-UY	PUP6004BU-WLPZ	PUP6XHD04BU-G
PUP6504GR-UY	PUP6004GR-WLPZ	PUP6XHD04GR-G
PUP6504RD-UY	PUP6004RD-WLPZ	PUP6XHD04RD-G
PUP6504OR-UY	PUP6004OR-WLPZ	PUP6XHD04OR-G
PUP6504VL-UY	PUP6004VL-WLPZ	PUP6XHD04VL-G
PUP6504WH-UY	PUP6004WH-WLPZ	PUP6XHD04WH-G
PUP6504YL-UY	PUP6004YL-WLPZ	PUP6XHD04YL-G
PUP6504BU-UY-S	PUP6004BU-WLPZ	PUP6XHD04BU-G
PUP6504WH-UY-S	PUP6004WH-WLPZ	PUP6XHD04WH-G
PUR6504BL-ULP	PUR6004BL-W	PUR6AV04BL-G
PUR6504BU-ULP	PUR6004BU-W	PUR6AV04BU-G
PUR6504IG-ULP	PUR6004IG-W	PUR6AV04IG-G
PUR6504GR-ULP	PUR6004GR-W	PUR6AV04GR-G
PUR6504RD-ULP	PUR6004RD-W	PUR6AV04RD-G
PUR6504OR-ULP	PUR6004OR-W	PUR6AV04OR-G
PUR6504VL-ULP	PUR6004VL-W	PUR6AV04VL-G
PUR6504WH-ULP	PUR6004WH-W	PUR6AV04WH-G
PUR6504YL-ULP	PUR6004YL-W	PUR6AV04YL-G
PUP6004WH-ULP	PUP6004WH-ULPZ	-
PUP6C04WH-W-S	PUP6C04WH-WZ	PUP6C04WH-WLPZ
PUP6C04BU-ULP	PUP6C04BU-WLPZ	PUP6C04BU-WZ
PUP6C04OR-ULP	PUP6C04OR-WLPZ	PUP6C04OR-WZ
PUP6C04YL-ULP	PUP6C04YL-WLPZ	PUP6C04YL-WZ
PUP6504IG-UY	PUP6004IG-WLPZ	PUP6XHD04IG-G
PUP6C04BU-W-S	PUP6C04BU-WZ	PUP6C04BU-WLPZ
PUP6C04WH-F	PUP6C04WH-WZ	PUP6C04WH-WLPZ
PUP6C04RD-F	PUP6C04RD-WZ	PUP6C04RD-WLPZ
PUP6C04BL-F	PUP6C04BL-WZ	PUP6C04BL-WLPZ