## Series TC 47 508P



## Pluggable Terminal Block with Screw Rising Clamp





3 Ways shown, various available

Current Rating	15 A
Voltage Rating	300 V
Dielectric Voltage Withstand	1600 V
Pitch Spacing	5.08 mm
Housing	PA66, UL94V-0
Temperature Range	-40°C ~ +105°C
Conductor Material	Copper Alloy, Nickel Plated
Wire Range	12-28 AWG
Wire Strip Length	7-8 mm
Screw Torque	0.6 Nm
Our Compatible Header Connectors	TC 47 508HV, TC 47 508HR Series

See Product Page for Diagram & Dimensions : www.thermodatacomponents.co.uk/PluggableTerminalBlock