

## Product information

# 00 21 33 E

## Tool Case "Robust26" Electric



- Ready when you are: for the toughest conditions – impact-resistant polypropylene, dustproof, waterproof and temperature-resistant
- Hard work becomes smart work: maximum flexibility due to 19 tool pockets and 61 retaining loops as well as adaptable aluminium divider system
- Convenient when you are on the move: fit-to-fly, with extendable handle and easy-running wheels for more comfort
- Fit-to-fly case, made from impact-resistant polypropylene
- Dustproof and watertight
- Air pressure compensation valve
- Temperature-resistant from - 30°C to +80° C
- Padlock eyelets
- Document compartment; tool boards made from dirt-repelling twin-wall PP sheet with tool pockets and tool straps
- Lockable base tray can be individually divided using aluminium separator system
- Ergonomic dual-component handle
- 19 tool pockets and 61 retaining loops
- Equipped with 16 KNIPEX tools, a total of 22 brand tools, partly VDE-tested according to DIN EN 60900
- Max. payload: 25 kg
- Volume: 26.4 litres

### General

Article No.	00 21 33 E
EAN	4003773089094
Weight	10,100 g
Dimensions	350 x 225 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Dimension exterior (interior) width mm	350 mm
Dimension exterior (interior) height mm	225 mm
Dimension exterior (interior) depth mm	550 mm

### Content

00 11 01	1 x KNIPEX TwinKey® for all standard cabinets and shut-off systems
00 21 33 LE	1 x Tool Case "Robust26" empty
08 26 185	1 x Needle-Nose Combination Pliers ⚠1000V 
12 52 195	1 x KNIPEX PreciStrip16 Automatic Insulation Stripper (0,08 - 16 mm <sup>2</sup> )
13 86 200	1 x Pliers for Electrical Installation (Ø 15 mm / 50 mm <sup>2</sup> ) ⚠1000V 
16 95 01 SB	1 x KNIPEX ErgoStrip® Universal Stripping Tool for right-handers (Ø 8,0 – 13,0 mm) 
26 26 200	1 x Snipe Nose Side Cutting Pliers (Stork Beak Pliers) ⚠1000V  $\angle 40^\circ$ 
70 06 160	1 x Diagonal Cutter ⚠1000V 

<b>Content</b>	
74 06 180	1 x High Leverage Diagonal Cutter ⚡1000V
78 06 125	1 x Electronic Super Knips® VDE ⚡1000V
90 22 10 BK	1 x KNIPEX BiX® Cutter for plastic pipes and sealing sleeves
97 53 14	1 x Self-Adjusting Crimping Pliers for wire ferrules with lateral access (0,08 – 16 mm²) 
98 20 35 SL	1 x Screwdriver (Slim) for slotted screws (3,5 mm) ⚡1000V
98 20 55 SL	1 x Screwdriver (Slim) for slotted screws (5,5 mm) ⚡1000V
98 25 01 SL	1 x Screwdriver (Slim) for cross-recessed screws Pozidriv® (PZ 1) ⚡1000V
98 25 01 SLS	1 x (Slim) PlusMinus screwdriver Pozidriv® (PZ/S 1) ⚡1000V
98 25 02 SL	1 x Screwdriver (Slim) for cross-recessed screws Pozidriv® (PZ 2) ⚡1000V
98 52	1 x Cable Knife ⚡1000V
01114	1 x Stabila Wooden folding rule type 1607, white, 2 m
101-0300	1 x Picard Locksmith's hammer (300 g)
18115	1 x Stabila Pocket Electric mini spirit level (68 mm)
2281	1 x Stabila spirit level type 70 (30 cm)
0022086	1 x Wera set of hex key wrenches (1,5 - 10 mm)

*technical change and errors excepted*