

Product information

00 21 33 S

Tool Case "Robust26" Plumbing



- Ready when you are: for the toughest conditions impact-resistant polypropylene, dustproof, waterproof and temperature-resistant
- Hard work becomes smart work: maximum flexibility due to 19 tool pockets and 61 retaining loops as well as adaptable aluminium divider system
- Convenient when you are on the move: fit-to-fly, with extendable handle and easy-running wheels for more comfort
- Fit-to-fly case, made from impact-resistant polypropylene
- Dustproof and watertight
- Air pressure compensation valve
- Temperature-resistant from 30°C to +80° C
- Padlock eyelets
- Document compartment; tool boards made from dirt-repelling twin-wall PP sheet with tool pockets and tool straps
- Lockable base tray can be individually divided using aluminium separator system
- Ergonomic dual-component handle
- 19 tool pockets and 61 retaining loops
- Equipped with 12 KNIPEX tools, a total of 17 brand tools, partly VDEtested according to DIN EN 60900
- Max. payload: 25 kgVolume: 26.4 litres

General	
Article No.	00 21 33 S
EAN	4003773089100
Dimensions	350 x 225 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

. to to compliant	
Content	
00 11 01	1 x KNIPEX TwinKey® for all standard cabinets and shut-off systems
00 21 33 LE	1 x Tool Case "Robust26" empty
74 06 180	1 x High Leverage Diagonal Cutter ≙ 1000 V ▶◀
86 03 300	1 x Pliers Wrench pliers and a wrench in a single tool
87 01 180	1 x KNIPEX Cobra® High-Tech Water Pump Pliers
87 01 300	1 x KNIPEX Cobra® High-Tech Water Pump Pliers
90 10 165 BK	1 x KNIPEX CutiX® Universal knife
90 22 10 BK	1 x KNIPEX BiX® Cutter for plastic pipes and sealing sleeves
90 31 02 SB	1 x KNIPEX TubiX® Pipe cutter
98 20 35 SL	1 x Screwdriver (Slim) for slotted screws (3,5 mm) ★ 1000 V ●
98 20 55 SL	1 x Screwdriver (Slim) for slotted screws (5,5 mm)
98 24 01 SL	1 x Screwdriver (Slim) for cross-recessed screws Phillips® (PH1) ≜ 1000 V ◆
98 24 02 SL	1 x Screwdriver (Slim) for cross-recessed screws Phillips® (PH2)

KNIPEX Quality – Made in Germany



Content	
	≙1000∨ •
01114	1 x Stabila Wooden folding rule type 1607, white, 2 m
101-0300	1 x Picard Locksmith's hammer (300 g)
2281	1 x Stabila spirit level type 70 (30 cm)
0022086	1 x Wera set of hex key wrenches (1,5 - 10 mm)

technical change and errors excepted