

Part-No. 244629-E

26-pin, SMT/IDC



Technical Data

Applications	Cable Connectors, PCB Connect ors,
Pitch	1.27 mm
No. of Pins	26
Termination	SMT/IDC
Current Rating	1.6 A
Max Operating Temperature	105 °C
Data Rate	3 Gbit/s
Air- and creepage distance	0.4 mm
Mating Cycles	500
Configuration	Connector
Packaging	Tape and reel 600 pcs

Part-No. 244629-E



26-pin, SMT/IDC